

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270085

Luminaire Tested: P3AS17R159740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270085
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 376.0 lumens
Efficiency: N/A
Efficacy: 17.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270085

CATALOG NUMBER: P3AS17R159740DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270085

CATALOG NUMBER: P3AS17R159740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162136
5°	149857
10°	119637
15°	90375
20°	68816
25°	52455
30°	37575
35°	24521
40°	15028
45°	9086
50°	6038
55°	4664
60°	4035
65°	3476
70°	3142
75°	3135
80°	2273
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9086 cd/sqm

TEST NUMBER: P1270085

CATALOG NUMBER: P3AS17R159740DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.3	16.0
10°-20°	111.3	29.6
20°-30°	99.1	26.3
30°-40°	58.6	15.6
40°-50°	24.1	6.4
50°-60°	11.3	3.0
60°-70°	6.9	1.8
70°-80°	3.6	1.0
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.6	72.0
0°-40°	329.3	87.6
0°-60°	364.6	97.0
0°-90°	376.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	376.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	739	
5°	681	60
15°	398	111
25°	217	99
35°	92	59
45°	29	24
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1270085

CATALOG NUMBER: P3AS17R159740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	739.4
1°	737.6
2°	732.1
3°	721.1
4°	702.8
5°	680.8
6°	657.0
7°	628.9
8°	599.6
9°	569.7
10°	537.3
12.5°	463.4
15°	398.1
17.5°	341.9
20°	294.9
22.5°	253.4
25°	216.8
27.5°	181.3
30°	148.4
32.5°	118.5
35°	91.6
37.5°	70.2
40°	52.5
42.5°	39.1
45°	29.3
47.5°	22.6
50°	17.7
52.5°	14.7
55°	12.2
57.5°	10.4
60°	9.2
62.5°	7.9
65°	6.7
67.5°	6.1
70°	4.9
72.5°	4.3
75°	3.7
77.5°	2.4
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)