

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270105

Luminaire Tested: P3AS17R209740DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270105
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209740DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 633.0 lumens
Efficiency: N/A
Efficacy: 29.9 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270105
CATALOG NUMBER: P3AS17R209740DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1270105
 CATALOG NUMBER: P3AS17R209740DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	487022
5°	442702
10°	327204
15°	202408
20°	115580
25°	65980
30°	37018
35°	20130
40°	11021
45°	6078
50°	3548
55°	2561
60°	2412
65°	2231
70°	1988
75°	2033
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6078 cd/sqm



TEST NUMBER: P1270105
 CATALOG NUMBER: P3AS17R209740DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.2	27.5
10°-20°	248.6	39.3
20°-30°	129.8	20.5
30°-40°	50.2	7.9
40°-50°	16.3	2.6
50°-60°	6.4	1.0
60°-70°	4.3	0.7
70°-80°	2.5	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	552.6	87.3
0°-40°	602.7	95.2
0°-60°	625.4	98.8
0°-90°	633.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	633.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2221	
5°	2011	174
15°	892	249
25°	273	130
35°	75	50
45°	20	16
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1270105
CATALOG NUMBER: P3AS17R209740DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2221.0
1°	2216.7
2°	2190.4
3°	2150.1
4°	2087.7
5°	2011.2
6°	1920.7
7°	1820.5
8°	1704.3
9°	1591.1
10°	1469.5
12.5°	1168.0
15°	891.6
17.5°	667.2
20°	495.3
22.5°	366.9
25°	272.7
27.5°	201.2
30°	146.2
32.5°	105.8
35°	75.2
37.5°	54.4
40°	38.5
42.5°	27.5
45°	19.6
47.5°	14.1
50°	10.4
52.5°	7.9
55°	6.7
57.5°	6.1
60°	5.5
62.5°	4.9
65°	4.3
67.5°	3.7
70°	3.1
72.5°	3.1
75°	2.4
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)