

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270188

Luminaire Tested: P3AS17R359740DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270188
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359740DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1583.9 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270188

CATALOG NUMBER: P3AS17R359740DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1270188

CATALOG NUMBER: P3AS17R359740DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83		
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78		
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75		
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73		
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1032878
5°	1011840
10°	941310
15°	690129
20°	353391
25°	127362
30°	49577
35°	17373
40°	7128
45°	1923
50°	1706
55°	1912
60°	1623
65°	1297
70°	1603
75°	2118
80°	1515
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 75°
Luminance: 2118 cd/sqm

TEST NUMBER: P1270188

CATALOG NUMBER: P3AS17R359740DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	428.5	27.1
10°-20°	804.0	50.8
20°-30°	284.7	18.0
30°-40°	49.8	3.1
40°-50°	7.3	0.5
50°-60°	4.0	0.3
60°-70°	2.9	0.2
70°-80°	2.1	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1517.2	95.8
0°-40°	1567.1	98.9
0°-60°	1578.4	99.7
0°-90°	1583.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1583.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4710	
5°	4597	429
15°	3040	804
25°	526	285
35°	65	50
45°	6	7
55°	5	4
65°	2	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1270188

CATALOG NUMBER: P3AS17R359740DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	4710.3
1°	4709.0
2°	4694.1
3°	4665.4
4°	4639.2
5°	4596.8
6°	4553.1
7°	4504.5
8°	4444.6
9°	4351.0
10°	4227.5
11°	4056.6
12°	3850.8
13°	3606.3
14°	3336.9
15°	3040.0
17.5°	2264.1
20°	1514.4
22.5°	913.1
25°	526.4
27.5°	314.4
30°	195.8
32.5°	113.5
35°	64.9
37.5°	41.2
40°	24.9
42.5°	12.5
45°	6.2
47.5°	5.0
50°	5.0
52.5°	5.0
55°	5.0
57.5°	3.7
60°	3.7
62.5°	3.7
65°	2.5
67.5°	2.5
70°	2.5
72.5°	2.5
75°	2.5
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0



TEST NUMBER: P1270188
CATALOG NUMBER: P3AS17R359740DE010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)