

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270197

Luminaire Tested: P3AS17R359740DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1270197  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R359740DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 495.0 lumens  
Efficiency: N/A  
Efficacy: 23.3 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270197  
CATALOG NUMBER: P3AS17R359740DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1270197  
 CATALOG NUMBER: P3AS17R359740DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	113083
5°	110675
10°	103650
15°	93031
20°	80927
25°	68956
30°	57781
35°	46016
40°	33262
45°	21056
50°	11462
55°	7952
60°	7499
65°	7005
70°	6668
75°	5676
80°	5430
85°	4529

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 21056 cd/sqm



TEST NUMBER: P1270197  
 CATALOG NUMBER: P3AS17R359740DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.8	9.5
10°-20°	114.0	23.0
20°-30°	130.7	26.4
30°-40°	106.6	21.5
40°-50°	53.8	10.9
50°-60°	20.0	4.0
60°-70°	13.4	2.7
70°-80°	7.4	1.5
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	291.5	58.9
0°-40°	398.2	80.4
0°-60°	471.9	95.3
0°-90°	495.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	495.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	516	
5°	503	47
15°	410	114
25°	285	131
35°	172	107
45°	68	54
55°	21	20
65°	14	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1270197  
CATALOG NUMBER: P3AS17R359740DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	515.7
1°	515.0
2°	513.8
3°	511.4
4°	507.7
5°	502.8
6°	496.7
7°	490.6
8°	482.6
9°	474.7
10°	465.5
11°	455.7
12°	445.3
13°	433.7
14°	421.5
15°	409.8
17.5°	378.6
20°	346.8
22.5°	314.4
25°	285.0
27.5°	256.3
30°	228.2
32.5°	200.0
35°	171.9
37.5°	143.7
40°	116.2
42.5°	90.5
45°	67.9
47.5°	48.9
50°	33.6
52.5°	24.5
55°	20.8
57.5°	19.0
60°	17.1
62.5°	15.3
65°	13.5
67.5°	11.6
70°	10.4
72.5°	8.6
75°	6.7
77.5°	5.5
80°	4.3
82.5°	3.1
85°	1.8
87.5°	1.2



TEST NUMBER: P1270197  
CATALOG NUMBER: P3AS17R359740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)