

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269481

Luminaire Tested: P3AS09R409740DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269481
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409740DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 520.9 lumens
Efficiency: N/A
Efficacy: 46.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269481

CATALOG NUMBER: P3AS09R409740DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1269481

CATALOG NUMBER: P3AS09R409740DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	91	94	92	89	92	89	88	86		
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80		
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74		
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69		
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	62	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162224
5°	158947
10°	147982
15°	128991
20°	103936
25°	77908
30°	54768
35°	35898
40°	21726
45°	12963
50°	7744
55°	6232
60°	5614
65°	4774
70°	4552
75°	3643
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12963 cd/sqm

TEST NUMBER: P1269481

CATALOG NUMBER: P3AS09R409740DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.1	12.9
10°-20°	156.5	30.0
20°-30°	147.5	28.3
30°-40°	85.3	16.4
40°-50°	34.0	6.5
50°-60°	15.0	2.9
60°-70°	9.3	1.8
70°-80°	4.9	0.9
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	371.0	71.2
0°-40°	456.3	87.6
0°-60°	505.3	97.0
0°-90°	520.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	520.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	740	
5°	722	67
15°	568	156
25°	322	147
35°	134	85
45°	42	34
55°	16	15
65°	9	9
75°	4	5
85°	1	2
90°	0	

TEST NUMBER: P1269481

CATALOG NUMBER: P3AS09R409740DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	739.8
2.5°	735.6
5°	722.1
7.5°	697.3
10°	664.6
12.5°	620.7
15°	568.2
17.5°	509.3
20°	445.4
22.5°	381.6
25°	322.0
27.5°	266.7
30°	216.3
32.5°	172.4
35°	134.1
37.5°	101.4
40°	75.9
42.5°	56.7
45°	41.8
47.5°	30.5
50°	22.7
52.5°	18.4
55°	16.3
57.5°	14.9
60°	12.8
62.5°	10.6
65°	9.2
67.5°	7.8
70°	7.1
72.5°	5.7
75°	4.3
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)