

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269494

Luminaire Tested: P3AS09R459740DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269494
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459740DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 792.0 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269494

CATALOG NUMBER: P3AS09R459740DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1269494

CATALOG NUMBER: P3AS09R459740DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	87	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	297432
5°	290446
10°	266996
15°	226244
20°	175529
25°	122693
30°	77303
35°	45508
40°	25763
45°	12528
50°	4332
55°	3517
60°	3421
65°	3321
70°	3206
75°	2965
80°	2652
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12528 cd/sqm

TEST NUMBER: P1269494

CATALOG NUMBER: P3AS09R459740DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.1	15.4
10°-20°	273.7	34.6
20°-30°	232.4	29.3
30°-40°	110.9	14.0
40°-50°	33.4	4.2
50°-60°	8.5	1.1
60°-70°	6.3	0.8
70°-80°	3.7	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	628.2	79.3
0°-40°	739.1	93.3
0°-60°	780.9	98.6
0°-90°	792.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	792.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1356	
5°	1320	122
15°	997	274
25°	507	232
35°	170	111
45°	40	33
55°	9	8
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1269494

CATALOG NUMBER: P3AS09R459740DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1356.4
2.5°	1347.9
5°	1319.5
7.5°	1270.7
10°	1199.1
12.5°	1104.2
15°	996.6
17.5°	876.9
20°	752.2
22.5°	625.4
25°	507.1
27.5°	399.5
30°	305.3
32.5°	229.5
35°	170.0
37.5°	125.4
40°	90.0
42.5°	62.3
45°	40.4
47.5°	22.7
50°	12.7
52.5°	9.9
55°	9.2
57.5°	8.5
60°	7.8
62.5°	7.1
65°	6.4
67.5°	5.7
70°	5.0
72.5°	4.2
75°	3.5
77.5°	2.8
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)