

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270248

Luminaire Tested: P3AS17R459740DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459740DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 683.0 lumens
Efficiency: N/A
Efficacy: 32.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270248

CATALOG NUMBER: P3AS17R459740DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270248

CATALOG NUMBER: P3AS17R459740DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	256493
5°	250473
10°	230256
15°	195098
20°	151376
25°	105804
30°	66668
35°	39244
40°	22213
45°	10792
50°	3753
55°	3020
60°	2938
65°	2854
70°	2757
75°	2626
80°	2273
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 10792 cd/sqm

TEST NUMBER: P1270248

CATALOG NUMBER: P3AS17R459740DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.3	15.4
10°-20°	236.0	34.6
20°-30°	200.4	29.3
30°-40°	95.6	14.0
40°-50°	28.8	4.2
50°-60°	7.3	1.1
60°-70°	5.4	0.8
70°-80°	3.2	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	541.7	79.3
0°-40°	637.3	93.3
0°-60°	673.4	98.6
0°-90°	683.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	683.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1170	
5°	1138	105
15°	859	236
25°	437	200
35°	147	96
45°	35	29
55°	8	7
65°	6	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1270248

CATALOG NUMBER: P3AS17R459740DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1169.7
2.5°	1162.4
5°	1137.9
7.5°	1095.8
10°	1034.1
12.5°	952.2
15°	859.4
17.5°	756.2
20°	648.7
22.5°	539.3
25°	437.3
27.5°	344.5
30°	263.3
32.5°	197.9
35°	146.6
37.5°	108.1
40°	77.6
42.5°	53.8
45°	34.8
47.5°	19.5
50°	11.0
52.5°	8.6
55°	7.9
57.5°	7.3
60°	6.7
62.5°	6.1
65°	5.5
67.5°	4.9
70°	4.3
72.5°	3.7
75°	3.1
77.5°	2.4
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)