

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269531

Luminaire Tested: P3AS09R509740DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269531
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509740DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 621.0 lumens
Efficiency: N/A
Efficacy: 55.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269531
CATALOG NUMBER: P3AS09R509740DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1269531
 CATALOG NUMBER: P3AS09R509740DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.9	8.5
10°-20°	135.2	21.8
20°-30°	164.2	26.4
30°-40°	139.3	22.4
40°-50°	72.4	11.7
50°-60°	26.1	4.2
60°-70°	18.1	2.9
70°-80°	9.8	1.6
80°-90°	3.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	352.3	56.7
0°-40°	491.6	79.2
0°-60°	590.1	95.0
0°-90°	621.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	621.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	576	
5°	565	53
15°	485	135
25°	359	164
35°	224	139
45°	94	72
55°	28	26
65°	18	18
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P1269531
CATALOG NUMBER: P3AS09R509740DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	575.5
2.5°	573.4
5°	564.9
7.5°	552.1
10°	533.7
12.5°	510.3
15°	484.8
17.5°	455.7
20°	423.8
22.5°	391.2
25°	359.3
27.5°	326.0
30°	292.0
32.5°	258.0
35°	224.0
37.5°	190.7
40°	157.3
42.5°	125.5
45°	93.6
47.5°	62.4
50°	40.4
52.5°	31.2
55°	28.4
57.5°	25.5
60°	23.4
62.5°	20.6
65°	18.4
67.5°	15.6
70°	13.5
72.5°	11.3
75°	9.2
77.5°	7.1
80°	5.7
82.5°	4.3
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)