

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270256

Luminaire Tested: P3AS17R459740DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270256
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459740DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1082.0 lumens
Efficiency: N/A
Efficacy: 51.0 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270256

CATALOG NUMBER: P3AS17R459740DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1270256

CATALOG NUMBER: P3AS17R459740DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75		
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69		
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63		
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50		
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47		
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	229411
5°	225335
10°	213245
15°	194485
20°	171958
25°	149331
30°	128197
35°	106809
40°	79606
45°	48718
50°	22549
55°	17624
60°	16972
65°	15514
70°	14361
75°	13725
80°	12628
85°	9309

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 48718 cd/sqm

TEST NUMBER: P1270256

CATALOG NUMBER: P3AS17R459740DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.6	8.8
10°-20°	238.5	22.0
20°-30°	283.4	26.2
30°-40°	246.2	22.8
40°-50°	123.5	11.4
50°-60°	42.9	4.0
60°-70°	30.1	2.8
70°-80°	16.8	1.6
80°-90°	5.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	617.5	57.1
0°-40°	863.7	79.8
0°-60°	1030.1	95.2
0°-90°	1082.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1082.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1046	
5°	1024	96
15°	857	239
25°	617	283
35°	399	246
45°	157	123
55°	46	43
65°	30	30
75°	16	17
85°	4	5
90°	0	

TEST NUMBER: P1270256

CATALOG NUMBER: P3AS17R459740DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1046.2
2.5°	1041.2
5°	1023.7
7.5°	996.3
10°	957.7
12.5°	910.3
15°	856.7
17.5°	796.8
20°	736.9
22.5°	675.8
25°	617.2
27.5°	561.1
30°	506.3
32.5°	453.9
35°	399.0
37.5°	340.4
40°	278.1
42.5°	217.0
45°	157.1
47.5°	103.5
50°	66.1
52.5°	51.1
55°	46.1
57.5°	42.4
60°	38.7
62.5°	34.9
65°	29.9
67.5°	26.2
70°	22.4
72.5°	18.7
75°	16.2
77.5°	12.5
80°	10.0
82.5°	7.5
85°	3.7
87.5°	2.5
90°	0.0

(END OF REPORT)