

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269535

Luminaire Tested: P3AS09R509740DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269535
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509740DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 523.0 lumens
Efficiency: N/A
Efficacy: 47.1 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269535

CATALOG NUMBER: P3AS09R509740DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1269535

CATALOG NUMBER: P3AS09R509740DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73		
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68		
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64		
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60		
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56		
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	152115
5°	148030
10°	136493
15°	120046
20°	100435
25°	79626
30°	58439
35°	40181
40°	25534
45°	14265
50°	7744
55°	6499
60°	5570
65°	5137
70°	4552
75°	4236
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14265 cd/sqm

TEST NUMBER: P1269535

CATALOG NUMBER: P3AS09R509740DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.3	11.9
10°-20°	146.4	28.0
20°-30°	149.8	28.6
30°-40°	95.0	18.2
40°-50°	37.8	7.2
50°-60°	15.3	2.9
60°-70°	9.8	1.9
70°-80°	5.0	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.5	68.6
0°-40°	453.5	86.7
0°-60°	506.6	96.9
0°-90°	523.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	523.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	694	
5°	672	62
15°	529	146
25°	329	150
35°	150	95
45°	46	38
55°	17	15
65°	10	10
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1269535

CATALOG NUMBER: P3AS09R509740DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	693.7
2.5°	688.7
5°	672.5
7.5°	647.0
10°	613.0
12.5°	572.6
15°	528.8
17.5°	480.6
20°	430.4
22.5°	380.1
25°	329.1
27.5°	278.2
30°	230.8
32.5°	188.3
35°	150.1
37.5°	117.5
40°	89.2
42.5°	65.8
45°	46.0
47.5°	31.1
50°	22.7
52.5°	19.1
55°	17.0
57.5°	14.9
60°	12.7
62.5°	11.3
65°	9.9
67.5°	8.5
70°	7.1
72.5°	5.7
75°	5.0
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)