

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270276

Luminaire Tested: P3AS17R509740DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509740DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1732.0 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270276

CATALOG NUMBER: P3AS17R509740DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1270276

CATALOG NUMBER: P3AS17R509740DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76
8	84	76	71	67	83	76	71	67	75	70	67		74	69	66		73
9	81	73	67	64	80	72	67	64	71	67	63		70	66	63		70
10	78	69	64	61	77	69	64	61	68	64	60		67	63	60		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	605259
5°	589147
10°	562225
15°	508970
20°	440338
25°	361206
30°	207500
35°	64460
40°	17318
45°	6078
50°	1467
55°	459
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6078 cd/sqm

TEST NUMBER: P1270276

CATALOG NUMBER: P3AS17R509740DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.7	14.5
10°-20°	621.2	35.9
20°-30°	652.9	37.7
30°-40°	186.9	10.8
40°-50°	18.3	1.1
50°-60°	1.5	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1524.9	88.0
0°-40°	1711.7	98.8
0°-60°	1731.5	100.0
0°-90°	1732.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1732.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2760	
5°	2676	251
15°	2242	621
25°	1493	653
35°	241	187
45°	20	18
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1270276

CATALOG NUMBER: P3AS17R509740DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2760.2
1°	2756.0
2°	2743.7
3°	2726.0
4°	2702.2
5°	2676.5
6°	2649.0
7°	2619.7
8°	2592.2
9°	2560.4
10°	2525.0
11°	2484.0
12°	2437.0
13°	2378.3
14°	2314.8
15°	2242.0
16°	2165.0
17°	2090.5
18°	2014.1
19°	1946.9
20°	1887.0
21°	1829.6
22°	1764.2
23°	1689.0
24°	1601.0
25°	1492.9
26°	1375.5
27°	1244.8
28°	1114.6
29°	974.1
30°	819.5
31°	674.6
32°	541.4
32.5°	483.4
33°	424.7
34°	325.7
35°	240.8
36°	176.6
37°	131.4
37.5°	113.7
38°	98.4
39°	76.4
40°	60.5
42.5°	34.2
45°	19.6



TEST NUMBER: P1270276

CATALOG NUMBER: P3AS17R509740DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	11.0
50°	4.3
52.5°	1.8
55°	1.2
57.5°	1.2
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)