

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269556

Luminaire Tested: P3AS09R559740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 294.0 lumens
Efficiency: N/A
Efficacy: 26.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269556

CATALOG NUMBER: P3AS09R559740DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1269556

CATALOG NUMBER: P3AS09R559740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	54	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55281
5°	54567
10°	52415
15°	49035
20°	44734
25°	39897
30°	34917
35°	28991
40°	22871
45°	15505
50°	9484
55°	4893
60°	4561
65°	4307
70°	4039
75°	3558
80°	3536
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15505 cd/sqm

TEST NUMBER: P1269556

CATALOG NUMBER: P3AS09R559740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.3	7.9
10°-20°	60.4	20.5
20°-30°	75.6	25.7
30°-40°	67.5	23.0
40°-50°	39.5	13.4
50°-60°	13.7	4.6
60°-70°	8.2	2.8
70°-80°	4.6	1.6
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	159.2	54.1
0°-40°	226.7	77.1
0°-60°	279.9	95.2
0°-90°	294.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	294.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	252	
5°	248	23
15°	216	60
25°	165	76
35°	108	67
45°	50	40
55°	13	14
65°	8	8
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1269556

CATALOG NUMBER: P3AS09R559740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	252.1
2.5°	250.7
5°	247.9
7.5°	242.4
10°	235.4
12.5°	226.7
15°	216.0
17.5°	204.5
20°	191.7
22.5°	178.5
25°	164.9
27.5°	151.4
30°	137.9
32.5°	123.3
35°	108.3
37.5°	93.8
40°	79.9
42.5°	64.9
45°	50.0
47.5°	38.2
50°	27.8
52.5°	18.1
55°	12.8
57.5°	11.5
60°	10.4
62.5°	9.4
65°	8.3
67.5°	7.3
70°	6.3
72.5°	5.2
75°	4.2
77.5°	3.5
80°	2.8
82.5°	1.7
85°	1.0
87.5°	0.7
90°	0.0

(END OF REPORT)