

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269561

Luminaire Tested: P3AS09R559740DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269561
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559740DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 600.0 lumens
Efficiency: N/A
Efficacy: 54.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269561

CATALOG NUMBER: P3AS09R559740DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269561

CATALOG NUMBER: P3AS09R559740DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	96		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112820
5°	111380
10°	106990
15°	100069
20°	91288
25°	81440
30°	71226
35°	59187
40°	46659
45°	31631
50°	19343
55°	10016
60°	9341
65°	8821
70°	8207
75°	7202
80°	7198
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31631 cd/sqm

TEST NUMBER: P1269561

CATALOG NUMBER: P3AS09R559740DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.5	7.9
10°-20°	123.2	20.5
20°-30°	154.3	25.7
30°-40°	137.7	23.0
40°-50°	80.6	13.4
50°-60°	27.8	4.6
60°-70°	16.8	2.8
70°-80°	9.3	1.6
80°-90°	2.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.9	54.2
0°-40°	462.6	77.1
0°-60°	571.1	95.2
0°-90°	600.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	600.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	514	
5°	506	47
15°	441	123
25°	337	154
35°	221	138
45°	102	81
55°	26	28
65°	17	17
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1269561

CATALOG NUMBER: P3AS09R559740DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	514.5
2.5°	511.6
5°	506.0
7.5°	494.6
10°	480.5
12.5°	462.7
15°	440.8
17.5°	417.4
20°	391.2
22.5°	364.2
25°	336.6
27.5°	309.0
30°	281.3
32.5°	251.6
35°	221.1
37.5°	191.3
40°	163.0
42.5°	132.5
45°	102.0
47.5°	78.0
50°	56.7
52.5°	36.8
55°	26.2
57.5°	23.4
60°	21.3
62.5°	19.1
65°	17.0
67.5°	14.9
70°	12.8
72.5°	10.6
75°	8.5
77.5°	7.1
80°	5.7
82.5°	3.5
85°	2.1
87.5°	1.4
90°	0.0

(END OF REPORT)