

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270295

Luminaire Tested: P3AS17R559740DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270295
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559740DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1660.0 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270295
CATALOG NUMBER: P3AS17R559740DE010 E3CB1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1270295

CATALOG NUMBER: P3AS17R559740DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94	94	94	94
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89	89	89	89
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84	84	84	84
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	86	83	80	79	79	79	79
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74	74	74	74
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70	70	70	70
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66	66	66	66
8	83	74	69	65	82	74	69	65	73	68	65	72	67	64	71	67	64	63	63	63	63
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60	60	60	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	460402
5°	456129
10°	474451
15°	467880
20°	431448
25°	351044
30°	213223
35°	73803
40°	21068
45°	10048
50°	4264
55°	1912
60°	2193
65°	1920
70°	1603
75°	2118
80°	1515
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10048 cd/sqm



TEST NUMBER: P1270295
 CATALOG NUMBER: P3AS17R559740DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.3	12.1
10°-20°	572.8	34.5
20°-30°	638.6	38.5
30°-40°	208.9	12.6
40°-50°	27.5	1.7
50°-60°	5.8	0.4
60°-70°	3.4	0.2
70°-80°	2.1	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1411.7	85.0
0°-40°	1620.6	97.6
0°-60°	1654.0	99.6
0°-90°	1660.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1660.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2100	
5°	2072	200
15°	2061	573
25°	1451	639
35°	276	209
45°	32	28
55°	5	6
65°	4	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1270295
CATALOG NUMBER: P3AS17R559740DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2099.6
2.5°	2084.7
5°	2072.2
7.5°	2102.1
10°	2130.8
12.5°	2115.9
15°	2061.0
17.5°	1973.6
20°	1848.9
22.5°	1676.7
25°	1450.9
27.5°	1164.0
30°	842.1
32.5°	516.5
35°	275.7
37.5°	139.7
40°	73.6
42.5°	47.4
45°	32.4
47.5°	22.5
50°	12.5
52.5°	7.5
55°	5.0
57.5°	5.0
60°	5.0
62.5°	3.7
65°	3.7
67.5°	2.5
70°	2.5
72.5°	2.5
75°	2.5
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)