

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270305

Luminaire Tested: P3AS17R559740DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559740DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1609.0 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270305

CATALOG NUMBER: P3AS17R559740DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1270305

CATALOG NUMBER: P3AS17R559740DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	98	94	90	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	84	98	92	87	84	90	86	83		88	84	82		86
5	95	88	83	79	94	87	82	78	85	81	78		84	80	77		82
6	91	83	78	74	90	82	77	74	81	76	73		80	76	73		78
7	87	79	73	70	86	78	73	69	77	72	69		76	72	69		75
8	83	75	69	66	82	74	69	66	73	69	65		72	68	65		71
9	80	71	66	62	79	71	66	62	70	65	62		69	65	62		68
10	77	68	62	59	76	67	62	59	67	62	59		66	62	59		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	466585
5°	450076
10°	466168
15°	459594
20°	425357
25°	344004
30°	206158
35°	69868
40°	19236
45°	8528
50°	2490
55°	459
60°	263
65°	311
70°	385
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8528 cd/sqm

TEST NUMBER: P1270305

CATALOG NUMBER: P3AS17R559740DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.8	12.3
10°-20°	563.7	35.0
20°-30°	626.6	38.9
30°-40°	195.0	12.1
40°-50°	23.4	1.5
50°-60°	1.8	0.1
60°-70°	0.6	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1388.0	86.3
0°-40°	1583.1	98.4
0°-60°	1608.3	100.0
0°-90°	1609.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1609.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2128	
5°	2045	198
15°	2024	564
25°	1422	627
35°	261	195
45°	28	23
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1270305

CATALOG NUMBER: P3AS17R559740DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2127.8
1°	2119.9
2°	2099.1
3°	2073.4
4°	2050.2
5°	2044.7
6°	2050.8
7°	2063.6
8°	2078.3
9°	2089.9
10°	2093.6
11°	2091.2
12°	2081.4
13°	2066.1
14°	2048.4
15°	2024.5
16°	1997.0
17°	1962.2
18°	1923.1
19°	1876.0
20°	1822.8
21°	1762.3
22°	1690.8
23°	1611.9
24°	1521.4
25°	1421.8
26°	1312.4
27°	1196.3
28°	1072.2
29°	944.4
30°	814.2
31°	683.4
32°	555.6
32.5°	498.8
33°	440.1
34°	340.5
35°	261.0
36°	198.7
37°	147.3
37.5°	125.9
38°	109.4
39°	83.1
40°	67.2
42.5°	42.8
45°	27.5



TEST NUMBER: P1270305

CATALOG NUMBER: P3AS17R559740DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	16.5
50°	7.3
52.5°	2.4
55°	1.2
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)