

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269590

Luminaire Tested: P3AS09R609740DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609740DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 584.0 lumens
Efficiency: N/A
Efficacy: 52.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269590

CATALOG NUMBER: P3AS09R609740DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269590

CATALOG NUMBER: P3AS09R609740DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103676
5°	102509
10°	98952
15°	93485
20°	86177
25°	78029
30°	69276
35°	59187
40°	47060
45°	33182
50°	19820
55°	10016
60°	9648
65°	8821
70°	8207
75°	7795
80°	7198
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33182 cd/sqm

TEST NUMBER: P1269590

CATALOG NUMBER: P3AS09R609740DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.8	7.5
10°-20°	115.1	19.7
20°-30°	147.8	25.3
30°-40°	137.0	23.5
40°-50°	83.4	14.3
50°-60°	27.8	4.8
60°-70°	16.9	2.9
70°-80°	9.5	1.6
80°-90°	2.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.6	52.5
0°-40°	443.6	76.0
0°-60°	554.8	95.0
0°-90°	584.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	584.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	473	
5°	466	44
15°	412	115
25°	322	148
35°	221	137
45°	107	83
55°	26	28
65°	17	17
75°	9	10
85°	2	3
90°	0	

TEST NUMBER: P1269590

CATALOG NUMBER: P3AS09R609740DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	472.8
2.5°	470.6
5°	465.7
7.5°	456.5
10°	444.4
12.5°	429.5
15°	411.8
17.5°	391.3
20°	369.3
22.5°	345.9
25°	322.5
27.5°	298.4
30°	273.6
32.5°	248.8
35°	221.1
37.5°	192.1
40°	164.4
42.5°	135.4
45°	107.0
47.5°	82.9
50°	58.1
52.5°	34.7
55°	26.2
57.5°	24.1
60°	22.0
62.5°	19.1
65°	17.0
67.5°	14.9
70°	12.8
72.5°	10.6
75°	9.2
77.5°	7.1
80°	5.7
82.5°	3.5
85°	2.1
87.5°	1.4
90°	0.0

(END OF REPORT)