

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269593

Luminaire Tested: P3AS09R609740DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609740DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 516.0 lumens
Efficiency: N/A
Efficacy: 46.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269593
CATALOG NUMBER: P3AS09R609740DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1269593
 CATALOG NUMBER: P3AS09R609740DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	130779
5°	127845
10°	119682
15°	107379
20°	92338
25°	76359
30°	60338
35°	44785
40°	30858
45°	19351
50°	10644
55°	6232
60°	5614
65°	4774
70°	4103
75°	4236
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19351 cd/sqm



TEST NUMBER: P1269593
 CATALOG NUMBER: P3AS09R609740DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.1	10.5
10°-20°	131.4	25.5
20°-30°	144.1	27.9
30°-40°	105.0	20.3
40°-50°	49.6	9.6
50°-60°	16.3	3.2
60°-70°	9.2	1.8
70°-80°	5.0	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	329.5	63.9
0°-40°	434.5	84.2
0°-60°	500.3	97.0
0°-90°	516.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	516.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	596	
5°	581	54
15°	473	131
25°	316	144
35°	167	105
45°	62	50
55°	16	16
65°	9	9
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1269593
CATALOG NUMBER: P3AS09R609740DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	596.4
2.5°	592.8
5°	580.8
7.5°	562.3
10°	537.5
12.5°	507.7
15°	473.0
17.5°	435.4
20°	395.7
22.5°	355.3
25°	315.6
27.5°	275.8
30°	238.3
32.5°	202.1
35°	167.3
37.5°	136.1
40°	107.8
42.5°	83.0
45°	62.4
47.5°	45.4
50°	31.2
52.5°	20.6
55°	16.3
57.5°	14.2
60°	12.8
62.5°	10.6
65°	9.2
67.5°	7.8
70°	6.4
72.5°	5.7
75°	5.0
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)