

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269598

Luminaire Tested: P3AS09R659740DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269598
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659740DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 877.0 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269598

CATALOG NUMBER: P3AS09R659740DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1269598

CATALOG NUMBER: P3AS09R659740DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		60	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	214325
5°	201716
10°	199150
15°	195642
20°	184699
25°	171445
30°	133261
35°	77095
40°	31058
45°	14296
50°	5561
55°	2179
60°	1886
65°	1816
70°	1795
75°	1779
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14296 cd/sqm

TEST NUMBER: P1269598

CATALOG NUMBER: P3AS09R659740DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.1	9.9
10°-20°	240.6	27.4
20°-30°	315.0	35.9
30°-40°	182.5	20.8
40°-50°	39.1	4.5
50°-60°	6.4	0.7
60°-70°	3.5	0.4
70°-80°	2.0	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	642.8	73.3
0°-40°	825.3	94.1
0°-60°	870.7	99.3
0°-90°	877.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	877.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	977	
5°	916	87
15°	862	241
25°	709	315
35°	288	182
45°	46	39
55°	6	6
65°	4	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1269598

CATALOG NUMBER: P3AS09R659740DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	977.4
2.5°	949.7
5°	916.4
7.5°	902.9
10°	894.4
12.5°	882.3
15°	861.8
17.5°	829.8
20°	791.5
22.5°	755.4
25°	708.6
27.5°	629.8
30°	526.3
32.5°	407.8
35°	288.0
37.5°	182.3
40°	108.5
42.5°	68.1
45°	46.1
47.5°	29.8
50°	16.3
52.5°	7.8
55°	5.7
57.5°	5.0
60°	4.3
62.5°	4.3
65°	3.5
67.5°	2.8
70°	2.8
72.5°	2.1
75°	2.1
77.5°	1.4
80°	1.4
82.5°	0.7
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)