

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270337

Luminaire Tested: P3AS17R609740DE010 E3DL1LI

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1270337  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R609740DE010 E3DL1LI  
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1312.0 lumens  
Efficiency: N/A  
Efficacy: 61.9 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270337

CATALOG NUMBER: P3AS17R609740DE010 E3DL1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1270337

CATALOG NUMBER: P3AS17R609740DE010 E3DL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  |
| 3   | 101 | 95  | 89  | 85  | 99  | 93  | 88  | 84  | 91  | 86  | 83  |  | 88  | 85  | 82  |  | 86  |
| 4   | 96  | 88  | 82  | 78  | 94  | 87  | 81  | 77  | 85  | 80  | 76  |  | 83  | 79  | 75  |  | 81  |
| 5   | 91  | 82  | 76  | 71  | 89  | 81  | 75  | 71  | 79  | 74  | 70  |  | 78  | 73  | 70  |  | 76  |
| 6   | 86  | 77  | 70  | 66  | 84  | 76  | 70  | 66  | 74  | 69  | 65  |  | 73  | 68  | 65  |  | 72  |
| 7   | 82  | 72  | 66  | 61  | 80  | 71  | 65  | 61  | 70  | 65  | 61  |  | 69  | 64  | 60  |  | 68  |
| 8   | 77  | 68  | 61  | 57  | 76  | 67  | 61  | 57  | 66  | 60  | 57  |  | 65  | 60  | 56  |  | 64  |
| 9   | 74  | 64  | 57  | 53  | 72  | 63  | 57  | 53  | 62  | 57  | 53  |  | 61  | 56  | 53  |  | 60  |
| 10  | 70  | 60  | 54  | 50  | 69  | 60  | 54  | 50  | 59  | 53  | 50  |  | 58  | 53  | 50  |  | 57  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 309800 |
| 5°  | 306867 |
| 10° | 297924 |
| 15° | 279116 |
| 20° | 247051 |
| 25° | 206673 |
| 30° | 161974 |
| 35° | 117490 |
| 40° | 78175  |
| 45° | 48718  |
| 50° | 26370  |
| 55° | 7646   |
| 60° | 7105   |
| 65° | 6486   |
| 70° | 6411   |
| 75° | 6354   |
| 80° | 6314   |
| 85° | 6290   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 48718 cd/sqm

TEST NUMBER: P1270337

CATALOG NUMBER: P3AS17R609740DE010 E3DL1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 131.3  | 10.0      |
| 10°-20°   | 341.1  | 26.0      |
| 20°-30°   | 388.8  | 29.6      |
| 30°-40°   | 275.7  | 21.0      |
| 40°-50°   | 125.1  | 9.5       |
| 50°-60°   | 26.6   | 2.0       |
| 60°-70°   | 12.8   | 1.0       |
| 70°-80°   | 7.9    | 0.6       |
| 80°-90°   | 2.7    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 861.2  | 65.6      |
| 0°-40°    | 1136.9 | 86.7      |
| 0°-60°    | 1288.6 | 98.2      |
| 0°-90°    | 1312.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1312.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1413 |      |
| 5°  | 1394 | 131  |
| 15° | 1230 | 341  |
| 25° | 854  | 389  |
| 35° | 439  | 276  |
| 45° | 157  | 125  |
| 55° | 20   | 27   |
| 65° | 12   | 13   |
| 75° | 8    | 8    |
| 85° | 2    | 3    |
| 90° | 0    |      |

TEST NUMBER: P1270337

CATALOG NUMBER: P3AS17R609740DE010 E3DL1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1412.8 |
| 2.5°  | 1407.8 |
| 5°    | 1394.1 |
| 7.5°  | 1370.4 |
| 10°   | 1338.0 |
| 12.5° | 1291.9 |
| 15°   | 1229.5 |
| 17.5° | 1151.0 |
| 20°   | 1058.7 |
| 22.5° | 958.9  |
| 25°   | 854.2  |
| 27.5° | 746.9  |
| 30°   | 639.7  |
| 32.5° | 537.4  |
| 35°   | 438.9  |
| 37.5° | 351.6  |
| 40°   | 273.1  |
| 42.5° | 207.0  |
| 45°   | 157.1  |
| 47.5° | 117.2  |
| 50°   | 77.3   |
| 52.5° | 36.2   |
| 55°   | 20.0   |
| 57.5° | 17.5   |
| 60°   | 16.2   |
| 62.5° | 15.0   |
| 65°   | 12.5   |
| 67.5° | 11.2   |
| 70°   | 10.0   |
| 72.5° | 8.7    |
| 75°   | 7.5    |
| 77.5° | 6.2    |
| 80°   | 5.0    |
| 82.5° | 3.7    |
| 85°   | 2.5    |
| 87.5° | 1.2    |
| 90°   | 0.0    |

(END OF REPORT)