

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269614

Luminaire Tested: P3AS09R659740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 273.9 lumens
Efficiency: N/A
Efficacy: 24.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269614
CATALOG NUMBER: P3AS09R659740DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1269614
 CATALOG NUMBER: P3AS09R659740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91	91	91	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82	82	82	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74	74	74	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67	67	67	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61	61	61	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56	56	56	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51	51	51	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47	47	47	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44	44	44	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48768
5°	48096
10°	46492
15°	43837
20°	40440
25°	36704
30°	32511
35°	27679
40°	22013
45°	15536
50°	9006
55°	4932
60°	4561
65°	4151
70°	3783
75°	3558
80°	3031
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15536 cd/sqm



TEST NUMBER: P1269614
 CATALOG NUMBER: P3AS09R659740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.6	7.5
10°-20°	54.0	19.7
20°-30°	69.4	25.3
30°-40°	64.3	23.5
40°-50°	38.8	14.1
50°-60°	13.2	4.8
60°-70°	8.0	2.9
70°-80°	4.5	1.6
80°-90°	1.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	144.0	52.6
0°-40°	208.3	76.0
0°-60°	260.2	95.0
0°-90°	273.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	273.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	222	
5°	218	21
15°	193	54
25°	152	69
35°	103	64
45°	50	39
55°	13	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1269614
CATALOG NUMBER: P3AS09R659740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	222.4
2.5°	221.3
5°	218.5
7.5°	214.4
10°	208.8
12.5°	201.8
15°	193.1
17.5°	183.7
20°	173.3
22.5°	162.5
25°	151.7
27.5°	140.2
30°	128.4
32.5°	116.6
35°	103.4
37.5°	90.5
40°	76.9
42.5°	63.3
45°	50.1
47.5°	37.9
50°	26.4
52.5°	16.7
55°	12.9
57.5°	11.5
60°	10.4
62.5°	9.0
65°	8.0
67.5°	7.0
70°	5.9
72.5°	5.2
75°	4.2
77.5°	3.5
80°	2.4
82.5°	1.7
85°	1.0
87.5°	0.7
90°	0.0

(END OF REPORT)