

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270347

Luminaire Tested: P3AS17R609740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 444.9 lumens
Efficiency: N/A
Efficacy: 21.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270347

CATALOG NUMBER: P3AS17R609740DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270347

CATALOG NUMBER: P3AS17R609740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112776
5°	110235
10°	103205
15°	92600
20°	79620
25°	65834
30°	52033
35°	38628
40°	26621
45°	16684
50°	9177
55°	5390
60°	4824
65°	4099
70°	3526
75°	3643
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16684 cd/sqm

TEST NUMBER: P1270347

CATALOG NUMBER: P3AS17R609740DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.6	10.5
10°-20°	113.3	25.5
20°-30°	124.3	27.9
30°-40°	90.5	20.3
40°-50°	42.7	9.6
50°-60°	14.0	3.1
60°-70°	7.9	1.8
70°-80°	4.3	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	284.2	63.9
0°-40°	374.7	84.2
0°-60°	431.4	97.0
0°-90°	444.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	444.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	514	
5°	501	47
15°	408	113
25°	272	124
35°	144	91
45°	54	43
55°	14	14
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1270347

CATALOG NUMBER: P3AS17R609740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	514.3
2.5°	511.2
5°	500.8
7.5°	484.9
10°	463.5
12.5°	437.9
15°	407.9
17.5°	375.5
20°	341.2
22.5°	306.4
25°	272.1
27.5°	237.9
30°	205.5
32.5°	174.3
35°	144.3
37.5°	117.4
40°	93.0
42.5°	71.5
45°	53.8
47.5°	39.1
50°	26.9
52.5°	17.7
55°	14.1
57.5°	12.2
60°	11.0
62.5°	9.2
65°	7.9
67.5°	6.7
70°	5.5
72.5°	4.9
75°	4.3
77.5°	3.1
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)