

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269619

Luminaire Tested: P3AS09R659740DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269619
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659740DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 558.0 lumens
Efficiency: N/A
Efficacy: 50.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269619

CATALOG NUMBER: P3AS09R659740DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269619

CATALOG NUMBER: P3AS09R659740DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99290
5°	97953
10°	94676
15°	89285
20°	82350
25°	74762
30°	66213
35°	56349
40°	44827
45°	31631
50°	18387
55°	10016
60°	9341
65°	8457
70°	7694
75°	7202
80°	6314
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31631 cd/sqm

TEST NUMBER: P1269619

CATALOG NUMBER: P3AS09R659740DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	7.5
10°-20°	110.0	19.7
20°-30°	141.4	25.3
30°-40°	130.8	23.4
40°-50°	79.0	14.2
50°-60°	26.9	4.8
60°-70°	16.2	2.9
70°-80°	9.2	1.6
80°-90°	2.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.3	52.6
0°-40°	424.1	76.0
0°-60°	530.0	95.0
0°-90°	558.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	558.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	453	
5°	445	42
15°	393	110
25°	309	141
35°	210	131
45°	102	79
55°	26	27
65°	16	16
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1269619

CATALOG NUMBER: P3AS09R659740DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	452.8
2.5°	450.7
5°	445.0
7.5°	436.5
10°	425.2
12.5°	411.0
15°	393.3
17.5°	374.2
20°	352.9
22.5°	330.9
25°	309.0
27.5°	285.6
30°	261.5
32.5°	237.4
35°	210.5
37.5°	184.3
40°	156.6
42.5°	129.0
45°	102.0
47.5°	77.2
50°	53.9
52.5°	34.0
55°	26.2
57.5°	23.4
60°	21.3
62.5°	18.4
65°	16.3
67.5°	14.2
70°	12.0
72.5°	10.6
75°	8.5
77.5°	7.1
80°	5.0
82.5°	3.5
85°	2.1
87.5°	1.4
90°	0.0

(END OF REPORT)