

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269625

Luminaire Tested: P3AS09R659740DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659740DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 491.0 lumens
Efficiency: N/A
Efficacy: 44.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269625

CATALOG NUMBER: P3AS09R659740DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269625

CATALOG NUMBER: P3AS09R659740DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	124815
5°	121703
10°	113336
15°	101567
20°	87718
25°	72972
30°	57528
35°	42643
40°	29369
45°	18234
50°	9893
55°	6232
60°	5263
65°	4774
70°	4103
75°	3558
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18234 cd/sqm

TEST NUMBER: P1269625

CATALOG NUMBER: P3AS09R659740DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.4	10.5
10°-20°	124.3	25.3
20°-30°	137.5	28.0
30°-40°	99.8	20.3
40°-50°	46.8	9.5
50°-60°	15.8	3.2
60°-70°	9.1	1.9
70°-80°	4.7	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	313.2	63.8
0°-40°	413.1	84.1
0°-60°	475.6	96.9
0°-90°	491.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	491.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	569	
5°	553	51
15°	447	124
25°	302	137
35°	159	100
45°	59	47
55°	16	16
65°	9	9
75°	4	5
85°	1	2
90°	0	

TEST NUMBER: P1269625

CATALOG NUMBER: P3AS09R659740DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	569.2
2.5°	565.6
5°	552.9
7.5°	533.8
10°	509.0
12.5°	480.0
15°	447.4
17.5°	412.0
20°	375.9
22.5°	338.4
25°	301.6
27.5°	264.0
30°	227.2
32.5°	191.8
35°	159.3
37.5°	129.5
40°	102.6
42.5°	78.6
45°	58.8
47.5°	42.5
50°	29.0
52.5°	19.8
55°	16.3
57.5°	14.2
60°	12.0
62.5°	10.6
65°	9.2
67.5°	7.8
70°	6.4
72.5°	5.7
75°	4.2
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)