

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270387

Luminaire Tested: P3AS17R709740DE010 E3CD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709740DE010 E3CD1MW
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 97CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1560.0 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270387

CATALOG NUMBER: P3AS17R709740DE010 E3CD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1270387

CATALOG NUMBER: P3AS17R709740DE010 E3CD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	309778
5°	295597
10°	281246
15°	273713
20°	263596
25°	249474
30°	232036
35°	194934
40°	125635
45°	58394
50°	15317
55°	3823
60°	3815
65°	3217
70°	3206
75°	3135
80°	3157
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 58394 cd/sqm

TEST NUMBER: P1270387

CATALOG NUMBER: P3AS17R709740DE010 E3CD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.7	8.1
10°-20°	338.8	21.7
20°-30°	473.3	30.3
30°-40°	438.9	28.1
40°-50°	157.3	10.1
50°-60°	13.3	0.9
60°-70°	6.6	0.4
70°-80°	4.3	0.3
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	937.8	60.1
0°-40°	1376.7	88.3
0°-60°	1547.4	99.2
0°-90°	1560.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1560.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1413	
5°	1343	126
15°	1206	339
25°	1031	473
35°	728	439
45°	188	157
55°	10	13
65°	6	7
75°	4	4
85°	1	2
90°	0	

TEST NUMBER: P1270387

CATALOG NUMBER: P3AS17R709740DE010 E3CD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1412.7
2.5°	1391.5
5°	1342.9
7.5°	1298.0
10°	1263.1
12.5°	1234.4
15°	1205.7
17.5°	1170.8
20°	1129.6
22.5°	1082.3
25°	1031.1
27.5°	978.8
30°	916.4
32.5°	836.6
35°	728.2
37.5°	589.8
40°	438.9
42.5°	299.2
45°	188.3
47.5°	104.7
50°	44.9
52.5°	15.0
55°	10.0
57.5°	8.7
60°	8.7
62.5°	7.5
65°	6.2
67.5°	6.2
70°	5.0
72.5°	5.0
75°	3.7
77.5°	3.7
80°	2.5
82.5°	2.5
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)