

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270488

Luminaire Tested: P3AS20R209740D010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1270488  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R209740D010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 632.0 lumens  
Efficiency: N/A  
Efficacy: 21.9 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270488  
CATALOG NUMBER: P3AS20R209740D010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1270488

CATALOG NUMBER: P3AS20R209740D010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83			83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76			76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65			65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55			55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52			52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48			48
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	156325
5°	152146
10°	139966
15°	123202
20°	105663
25°	88771
30°	71758
35°	54582
40°	38844
45°	25646
50°	15897
55°	10437
60°	9517
65°	8769
70°	8207
75°	7456
80°	7072
85°	6038

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25646 cd/sqm



TEST NUMBER: P1270488  
 CATALOG NUMBER: P3AS20R209740D010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.9	10.1
10°-20°	151.1	23.9
20°-30°	167.7	26.5
30°-40°	127.9	20.2
40°-50°	65.5	10.4
50°-60°	26.9	4.3
60°-70°	16.8	2.7
70°-80°	9.4	1.5
80°-90°	2.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	382.7	60.6
0°-40°	510.7	80.8
0°-60°	603.1	95.4
0°-90°	632.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	632.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	713	
5°	691	64
15°	543	151
25°	367	168
35°	204	128
45°	83	66
55°	27	27
65°	17	17
75°	9	9
85°	2	3
90°	0	



TEST NUMBER: P1270488  
CATALOG NUMBER: P3AS20R209740D010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	712.9
1°	713.7
2°	710.5
3°	706.5
4°	700.1
5°	691.2
6°	680.8
7°	669.5
8°	657.5
9°	643.1
10°	628.6
12.5°	586.9
15°	542.7
17.5°	497.7
20°	452.8
22.5°	407.8
25°	366.9
27.5°	325.9
30°	283.4
32.5°	243.3
35°	203.9
37.5°	169.4
40°	135.7
42.5°	106.8
45°	82.7
47.5°	62.6
50°	46.6
52.5°	34.5
55°	27.3
57.5°	24.9
60°	21.7
62.5°	19.3
65°	16.9
67.5°	14.5
70°	12.8
72.5°	10.4
75°	8.8
77.5°	7.2
80°	5.6
82.5°	4.0
85°	2.4
87.5°	0.8
90°	0.0

(END OF REPORT)