

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269710

Luminaire Tested: P3AS13R129740DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1269710  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R129740DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R12 optic, 4000K CCT AND, 97CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 526.0 lumens  
Efficiency: N/A  
Efficacy: 33.9 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1269710  
CATALOG NUMBER: P3AS13R129740DE010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1269710  
 CATALOG NUMBER: P3AS13R129740DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	226824
5°	209641
10°	167376
15°	126425
20°	96282
25°	73359
30°	52565
35°	34291
40°	21039
45°	12714
50°	8460
55°	6537
60°	5614
65°	4877
70°	4360
75°	4321
80°	3283
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12714 cd/sqm



TEST NUMBER: P1269710  
 CATALOG NUMBER: P3AS13R129740DE010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.4	16.0
10°-20°	155.7	29.6
20°-30°	138.6	26.3
30°-40°	82.0	15.6
40°-50°	33.7	6.4
50°-60°	15.8	3.0
60°-70°	9.6	1.8
70°-80°	5.1	1.0
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	378.6	72.0
0°-40°	460.6	87.6
0°-60°	510.1	97.0
0°-90°	526.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	526.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1034	
5°	952	84
15°	557	156
25°	303	139
35°	128	82
45°	41	34
55°	17	16
65°	9	10
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1269710  
CATALOG NUMBER: P3AS13R129740DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1034.4
1°	1031.8
2°	1024.1
3°	1008.8
4°	983.1
5°	952.4
6°	919.1
7°	879.8
8°	838.8
9°	796.9
10°	751.7
12.5°	648.3
15°	556.9
17.5°	478.3
20°	412.6
22.5°	354.5
25°	303.2
27.5°	253.7
30°	207.6
32.5°	165.7
35°	128.1
37.5°	98.2
40°	73.5
42.5°	54.7
45°	41.0
47.5°	31.6
50°	24.8
52.5°	20.5
55°	17.1
57.5°	14.5
60°	12.8
62.5°	11.1
65°	9.4
67.5°	8.5
70°	6.8
72.5°	6.0
75°	5.1
77.5°	3.4
80°	2.6
82.5°	1.7
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)