

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270497

Luminaire Tested: P3AS20R209740D010 E3PHLP1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1270497  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R209740D010 E3PHLP1MW  
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 97CRI , E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 802.0 lumens  
Efficiency: N/A  
Efficacy: 27.8 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270497  
CATALOG NUMBER: P3AS20R209740D010 E3PHLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1270497  
 CATALOG NUMBER: P3AS20R209740D010 E3PHLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90			90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68			68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63			63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55			55
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52			52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49
10	69	59	52	48	68	58	52	48	57	52	48	57	52	48	56	51	48	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	285196
5°	266035
10°	220749
15°	168786
20°	126688
25°	95376
30°	70517
35°	49282
40°	33778
45°	23413
50°	20127
55°	19842
60°	20700
65°	20806
70°	21157
75°	22028
80°	23867
85°	23650

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 27720 cd/sqm



TEST NUMBER: P1270497  
 CATALOG NUMBER: P3AS20R209740D010 E3PHLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.3	13.5
10°-20°	206.7	25.8
20°-30°	181.9	22.7
30°-40°	117.4	14.6
40°-50°	62.2	7.8
50°-60°	46.8	5.8
60°-70°	39.8	5.0
70°-80°	28.0	3.5
80°-90°	10.9	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	496.9	62.0
0°-40°	614.3	76.6
0°-60°	723.3	90.2
0°-90°	802.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	802.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1301	
5°	1209	108
15°	744	207
25°	394	182
35°	184	117
45°	76	62
55°	52	47
65°	40	40
75°	26	28
85°	9	11
90°	0	



TEST NUMBER: P1270497  
CATALOG NUMBER: P3AS20R209740D010 E3PHLP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1300.6
2.5°	1274.6
5°	1208.6
7.5°	1107.1
10°	991.4
12.5°	863.9
15°	743.5
17.5°	635.0
20°	542.9
22.5°	465.0
25°	394.2
27.5°	332.8
30°	278.5
32.5°	229.0
35°	184.1
37.5°	148.7
40°	118.0
42.5°	94.4
45°	75.5
47.5°	66.1
50°	59.0
52.5°	54.3
55°	51.9
57.5°	49.6
60°	47.2
62.5°	42.5
65°	40.1
67.5°	37.8
70°	33.0
72.5°	30.7
75°	26.0
77.5°	23.6
80°	18.9
82.5°	16.5
85°	9.4
87.5°	4.7
90°	0.0

(END OF REPORT)