

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269755

Luminaire Tested: P3AS13R209740DE010 E3D1H

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1269755  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R209740DE010 E3D1H  
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 97CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1180.1 lumens  
Efficiency: N/A  
Efficacy: 80.8 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1269755  
CATALOG NUMBER: P3AS13R209740DE010 E3D1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1269755  
 CATALOG NUMBER: P3AS13R209740DE010 E3D1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	100
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	98	97	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96	99	98	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	97	95	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	95	93	95	93	92	95	93	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90	93	91	90	89
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	92	89	88	92	89	88	87
7	99	93	90	87	98	93	89	87	92	89	86	91	88	86	90	87	86	90	87	86	85
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84	88	86	84	83
9	95	89	85	83	94	89	85	83	88	85	83	87	84	83	87	84	82	87	84	82	81
10	93	87	84	81	92	87	83	81	86	83	81	86	83	81	85	83	81	85	83	81	80

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1789966
5°	1507062
10°	941310
15°	351920
20°	120784
25°	50350
30°	23725
35°	10627
40°	5009
45°	2574
50°	955
55°	191
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2574 cd/sqm



TEST NUMBER: P1269755  
 CATALOG NUMBER: P3AS13R209740DE010 E3D1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	569.4	48.2
10°-20°	469.0	39.7
20°-30°	106.6	9.0
30°-40°	27.1	2.3
40°-50°	6.8	0.6
50°-60°	0.9	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1144.9	97.0
0°-40°	1172.1	99.3
0°-60°	1179.8	100.0
0°-90°	1180.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1180.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8163	
5°	6847	569
15°	1550	469
25°	208	107
35°	40	27
45°	8	7
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1269755  
CATALOG NUMBER: P3AS13R209740DE010 E3D1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8162.9
1°	8093.7
2°	7889.8
3°	7597.3
4°	7238.3
5°	6846.6
6°	6410.2
7°	5928.5
8°	5366.6
9°	4809.7
10°	4227.5
11°	3607.9
12°	2989.2
13°	2465.1
14°	1964.0
15°	1550.2
16°	1223.5
17°	965.2
18°	775.6
19°	630.7
20°	517.6
21°	432.8
22°	361.2
23°	300.3
24°	250.5
25°	208.1
27.5°	136.1
30°	93.7
32.5°	57.7
35°	39.7
37.5°	25.4
40°	17.5
42.5°	12.0
45°	8.3
47.5°	5.5
50°	2.8
52.5°	1.4
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1269755  
CATALOG NUMBER: P3AS13R209740DE010 E3D1H

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)