

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270509

Luminaire Tested: P3AS20R259740D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270509
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R259740D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 839.9 lumens
Efficiency: N/A
Efficacy: 29.2 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270509

CATALOG NUMBER: P3AS20R259740D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270509

CATALOG NUMBER: P3AS20R259740D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	538838
5°	502728
10°	402709
15°	273350
20°	165401
25°	96731
30°	55072
35°	30303
40°	16087
45°	8466
50°	4912
55°	3670
60°	3158
65°	3321
70°	3077
75°	2711
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8466 cd/sqm

TEST NUMBER: P1270509

CATALOG NUMBER: P3AS20R259740D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.7	24.1
10°-20°	331.0	39.4
20°-30°	189.2	22.5
30°-40°	74.6	8.9
40°-50°	22.9	2.7
50°-60°	9.0	1.1
60°-70°	6.0	0.7
70°-80°	3.4	0.4
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	722.9	86.1
0°-40°	797.5	95.0
0°-60°	829.4	98.7
0°-90°	839.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	839.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2457	
5°	2284	203
15°	1204	331
25°	400	189
35°	113	75
45°	27	23
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1270509

CATALOG NUMBER: P3AS20R259740D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2457.3
1°	2452.4
2°	2432.4
3°	2397.0
4°	2348.1
5°	2283.9
6°	2208.4
7°	2123.3
8°	2024.6
9°	1923.4
10°	1808.6
11°	1695.4
12°	1571.0
13°	1448.2
14°	1322.1
15°	1204.1
17.5°	933.6
20°	708.8
22.5°	532.2
25°	399.8
27.5°	296.2
30°	217.5
32.5°	157.3
35°	113.2
37.5°	80.3
40°	56.2
42.5°	38.5
45°	27.3
47.5°	19.3
50°	14.4
52.5°	11.2
55°	9.6
57.5°	8.8
60°	7.2
62.5°	6.4
65°	6.4
67.5°	5.6
70°	4.8
72.5°	4.0
75°	3.2
77.5°	2.4
80°	1.6
82.5°	1.6
85°	0.8
87.5°	0.8



TEST NUMBER: P1270509

CATALOG NUMBER: P3AS20R259740D010 E3DL1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)