

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269797

Luminaire Tested: P3AS13R259740DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269797
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259740DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 756.0 lumens
Efficiency: N/A
Efficacy: 51.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269797

CATALOG NUMBER: P3AS13R259740DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1269797

CATALOG NUMBER: P3AS13R259740DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	179679
5°	175390
10°	162522
15°	144745
20°	124401
25°	105732
30°	87051
35°	67806
40°	48806
45°	30949
50°	18319
55°	12616
60°	11578
65°	10740
70°	9681
75°	8811
80°	8334
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30949 cd/sqm

TEST NUMBER: P1269797

CATALOG NUMBER: P3AS13R259740DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.9	9.8
10°-20°	177.0	23.4
20°-30°	200.0	26.5
30°-40°	158.2	20.9
40°-50°	79.9	10.6
50°-60°	32.0	4.2
60°-70°	20.5	2.7
70°-80°	11.3	1.5
80°-90°	3.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	450.9	59.6
0°-40°	609.1	80.6
0°-60°	721.0	95.4
0°-90°	756.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	756.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	819	
5°	797	74
15°	638	177
25°	437	200
35°	253	158
45°	100	80
55°	33	32
65°	21	20
75°	10	11
85°	3	3
90°	0	

TEST NUMBER: P1269797

CATALOG NUMBER: P3AS13R259740DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	819.4
1°	819.4
2°	816.6
3°	811.8
4°	805.3
5°	796.8
6°	786.4
7°	774.2
8°	761.0
9°	745.9
10°	729.9
11°	712.0
12°	695.1
13°	675.3
14°	656.4
15°	637.6
17.5°	584.9
20°	533.1
22.5°	484.1
25°	437.0
27.5°	390.9
30°	343.8
32.5°	299.5
35°	253.3
37.5°	211.0
40°	170.5
42.5°	132.8
45°	99.8
47.5°	74.4
50°	53.7
52.5°	40.5
55°	33.0
57.5°	30.1
60°	26.4
62.5°	23.5
65°	20.7
67.5°	17.9
70°	15.1
72.5°	13.2
75°	10.4
77.5°	8.5
80°	6.6
82.5°	4.7
85°	2.8
87.5°	0.9



TEST NUMBER: P1269797

CATALOG NUMBER: P3AS13R259740DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)