

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270533

Luminaire Tested: P3AS20R309740D010 E3CD1MB

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1270533  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R309740D010 E3CD1MB  
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2084.0 lumens  
Efficiency: N/A  
Efficacy: 72.4 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270533  
CATALOG NUMBER: P3AS20R309740D010 E3CD1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1270533  
 CATALOG NUMBER: P3AS20R309740D010 E3CD1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	98	97	97	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	95	94	94	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	93	91	91	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	87	91	88	87	85
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	89	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	84	82	80	79
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	82	79	77	77
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	77	75	80	77	75	75

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1697079
5°	1664997
10°	1473965
15°	933831
20°	354464
25°	104958
30°	41449
35°	12715
40°	5611
45°	2016
50°	1672
55°	1262
60°	1447
65°	1712
70°	1026
75°	1356
80°	2020
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 80°  
 Luminance: 2020 cd/sqm



TEST NUMBER: P1270533  
 CATALOG NUMBER: P3AS20R309740D010 E3CD1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	695.3	33.4
10°-20°	1083.7	52.0
20°-30°	251.6	12.1
30°-40°	39.0	1.9
40°-50°	6.7	0.3
50°-60°	3.1	0.2
60°-70°	2.6	0.1
70°-80°	1.7	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2030.7	97.4
0°-40°	2069.6	99.3
0°-60°	2079.4	99.8
0°-90°	2084.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2084.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7739	
5°	7564	695
15°	4114	1084
25°	434	252
35°	48	39
45°	6	7
55°	3	3
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1270533  
CATALOG NUMBER: P3AS20R309740D010 E3CD1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7739.3
1°	7734.4
2°	7713.1
3°	7677.1
4°	7631.3
5°	7564.1
6°	7480.7
7°	7356.3
8°	7186.0
9°	6935.6
10°	6619.7
11°	6212.1
12°	5752.1
13°	5241.4
14°	4679.9
15°	4113.5
17.5°	2691.1
20°	1519.0
22.5°	775.9
25°	433.8
27.5°	266.8
30°	163.7
32.5°	88.4
35°	47.5
37.5°	31.1
40°	19.6
42.5°	11.5
45°	6.5
47.5°	4.9
50°	4.9
52.5°	3.3
55°	3.3
57.5°	3.3
60°	3.3
62.5°	3.3
65°	3.3
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	1.6
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1270533  
CATALOG NUMBER: P3AS20R309740D010 E3CD1MB

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)