

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269846

Luminaire Tested: P3AS13R359740DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269846
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359740DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 485.0 lumens
Efficiency: N/A
Efficacy: 33.2 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269846
CATALOG NUMBER: P3AS13R359740DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1269846

CATALOG NUMBER: P3AS13R359740DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	244608
5°	235086
10°	204828
15°	156891
20°	104962
25°	63512
30°	36436
35°	20371
40°	10820
45°	5582
50°	2661
55°	2103
60°	2017
65°	1660
70°	1795
75°	1525
80°	1768
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5582 cd/sqm



TEST NUMBER: P1269846
 CATALOG NUMBER: P3AS13R359740DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.2	20.0
10°-20°	188.3	38.8
20°-30°	123.3	25.4
30°-40°	50.0	10.3
40°-50°	15.0	3.1
50°-60°	5.1	1.0
60°-70°	3.4	0.7
70°-80°	2.0	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	408.8	84.3
0°-40°	458.8	94.6
0°-60°	478.9	98.7
0°-90°	485.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	485.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1116	
5°	1068	97
15°	691	188
25°	262	123
35°	76	50
45°	18	15
55°	6	5
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1269846
CATALOG NUMBER: P3AS13R359740DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1115.5
1°	1113.7
2°	1108.6
3°	1098.5
4°	1086.5
5°	1068.0
6°	1044.9
7°	1019.1
8°	990.0
9°	956.8
10°	919.9
11°	878.9
12°	836.0
13°	788.0
14°	742.3
15°	691.1
17.5°	567.0
20°	449.8
22.5°	346.0
25°	262.5
27.5°	195.6
30°	143.9
32.5°	105.6
35°	76.1
37.5°	54.0
40°	37.8
42.5°	26.3
45°	18.0
47.5°	12.0
50°	7.8
52.5°	6.0
55°	5.5
57.5°	5.1
60°	4.6
62.5°	4.2
65°	3.2
67.5°	2.8
70°	2.8
72.5°	2.3
75°	1.8
77.5°	1.4
80°	1.4
82.5°	0.9
85°	0.5
87.5°	0.5



TEST NUMBER: P1269846
CATALOG NUMBER: P3AS13R359740DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)