

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269847

Luminaire Tested: P3AS13R359740DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269847
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359740DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 989.0 lumens
Efficiency: N/A
Efficacy: 67.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269847
CATALOG NUMBER: P3AS13R359740DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1269847
 CATALOG NUMBER: P3AS13R359740DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 | 102 | 100 | 99 | 98 | 97 | 96 | 95 | 95 | 95 | 95 |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 97 | 95 | 97 | 95 | 93 | 94 | 93 | 91 | 90 | 90 | 90 | 90 |
| 3 | 105 | 99 | 95 | 91 | 103 | 98 | 94 | 90 | 95 | 92 | 89 | 93 | 90 | 88 | 91 | 88 | 86 | 85 | 85 | 85 | 85 |
| 4 | 100 | 94 | 89 | 85 | 99 | 93 | 88 | 85 | 91 | 87 | 84 | 89 | 85 | 83 | 87 | 84 | 82 | 80 | 80 | 80 | 80 |
| 5 | 96 | 89 | 84 | 80 | 95 | 88 | 83 | 80 | 86 | 82 | 79 | 85 | 81 | 78 | 83 | 80 | 78 | 77 | 77 | 77 | 77 |
| 6 | 92 | 85 | 80 | 76 | 91 | 84 | 79 | 76 | 83 | 78 | 75 | 81 | 77 | 75 | 80 | 77 | 74 | 73 | 73 | 73 | 73 |
| 7 | 89 | 81 | 76 | 72 | 88 | 80 | 75 | 72 | 79 | 75 | 71 | 78 | 74 | 71 | 77 | 73 | 71 | 70 | 70 | 70 | 70 |
| 8 | 85 | 77 | 72 | 69 | 84 | 77 | 72 | 69 | 76 | 71 | 68 | 75 | 71 | 68 | 74 | 70 | 68 | 67 | 67 | 67 | 67 |
| 9 | 82 | 74 | 69 | 66 | 81 | 74 | 69 | 65 | 73 | 68 | 65 | 72 | 68 | 65 | 71 | 68 | 65 | 64 | 64 | 64 | 64 |
| 10 | 79 | 71 | 66 | 63 | 78 | 71 | 66 | 63 | 70 | 66 | 63 | 69 | 65 | 62 | 69 | 65 | 62 | 61 | 61 | 61 | 61 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 498798 |
| 5° | 479396 |
| 10° | 417694 |
| 15° | 319934 |
| 20° | 214032 |
| 25° | 129516 |
| 30° | 74315 |
| 35° | 41546 |
| 40° | 22070 |
| 45° | 11381 |
| 50° | 5458 |
| 55° | 4320 |
| 60° | 4122 |
| 65° | 3424 |
| 70° | 3590 |
| 75° | 3219 |
| 80° | 3536 |
| 85° | 2264 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11381 cd/sqm



TEST NUMBER: P1269847
 CATALOG NUMBER: P3AS13R359740DE010 E3DL1H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 198.2 | 20.0 |
| 10°-20° | 384.0 | 38.8 |
| 20°-30° | 251.4 | 25.4 |
| 30°-40° | 102.0 | 10.3 |
| 40°-50° | 30.6 | 3.1 |
| 50°-60° | 10.4 | 1.0 |
| 60°-70° | 7.0 | 0.7 |
| 70°-80° | 4.1 | 0.4 |
| 80°-90° | 1.4 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 833.6 | 84.3 |
| 0°-40° | 935.5 | 94.6 |
| 0°-60° | 976.5 | 98.7 |
| 0°-90° | 989.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 989.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2275 | |
| 5° | 2178 | 198 |
| 15° | 1409 | 384 |
| 25° | 535 | 251 |
| 35° | 155 | 102 |
| 45° | 37 | 31 |
| 55° | 11 | 10 |
| 65° | 7 | 7 |
| 75° | 4 | 4 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P1269847
CATALOG NUMBER: P3AS13R359740DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 2274.7 |
| 1° | 2271.0 |
| 2° | 2260.6 |
| 3° | 2239.9 |
| 4° | 2215.5 |
| 5° | 2177.9 |
| 6° | 2130.8 |
| 7° | 2078.1 |
| 8° | 2018.9 |
| 9° | 1951.1 |
| 10° | 1875.9 |
| 11° | 1792.1 |
| 12° | 1704.7 |
| 13° | 1606.8 |
| 14° | 1513.7 |
| 15° | 1409.3 |
| 17.5° | 1156.2 |
| 20° | 917.2 |
| 22.5° | 705.6 |
| 25° | 535.3 |
| 27.5° | 398.9 |
| 30° | 293.5 |
| 32.5° | 215.4 |
| 35° | 155.2 |
| 37.5° | 110.1 |
| 40° | 77.1 |
| 42.5° | 53.6 |
| 45° | 36.7 |
| 47.5° | 24.5 |
| 50° | 16.0 |
| 52.5° | 12.2 |
| 55° | 11.3 |
| 57.5° | 10.3 |
| 60° | 9.4 |
| 62.5° | 8.5 |
| 65° | 6.6 |
| 67.5° | 5.6 |
| 70° | 5.6 |
| 72.5° | 4.7 |
| 75° | 3.8 |
| 77.5° | 2.8 |
| 80° | 2.8 |
| 82.5° | 1.9 |
| 85° | 0.9 |
| 87.5° | 0.9 |



TEST NUMBER: P1269847
CATALOG NUMBER: P3AS13R359740DE010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)