

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270638

Luminaire Tested: P3AS20R459740D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270638
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459740D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 579.0 lumens
Efficiency: N/A
Efficacy: 20.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270638

CATALOG NUMBER: P3AS20R459740D010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1270638

CATALOG NUMBER: P3AS20R459740D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		86
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		79
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		74
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		64
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		60
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		56
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		53
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	172464
5°	168523
10°	155464
15°	135188
20°	111053
25°	86400
30°	63807
35°	44892
40°	28024
45°	15195
50°	8221
55°	7073
60°	6315
65°	5396
70°	4616
75°	4745
80°	4041
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15195 cd/sqm

TEST NUMBER: P1270638

CATALOG NUMBER: P3AS20R459740D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.9	12.2
10°-20°	164.6	28.4
20°-30°	163.4	28.2
30°-40°	105.3	18.2
40°-50°	40.5	7.0
50°-60°	16.5	2.9
60°-70°	10.4	1.8
70°-80°	5.6	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	399.0	68.9
0°-40°	504.2	87.1
0°-60°	561.3	96.9
0°-90°	579.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	579.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	786	
5°	766	71
15°	596	165
25°	357	163
35°	168	105
45°	49	41
55°	18	17
65°	10	10
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1270638

CATALOG NUMBER: P3AS20R459740D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	786.5
2.5°	782.5
5°	765.6
7.5°	736.7
10°	698.2
12.5°	650.1
15°	595.5
17.5°	536.1
20°	475.9
22.5°	414.9
25°	357.1
27.5°	302.6
30°	252.0
32.5°	207.9
35°	167.7
37.5°	131.6
40°	97.9
42.5°	70.6
45°	49.0
47.5°	32.9
50°	24.1
52.5°	20.1
55°	18.5
57.5°	16.1
60°	14.4
62.5°	12.0
65°	10.4
67.5°	8.8
70°	7.2
72.5°	6.4
75°	5.6
77.5°	4.0
80°	3.2
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)