

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269915

Luminaire Tested: P3AS13R459740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 333.0 lumens
Efficiency: N/A
Efficacy: 22.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269915

CATALOG NUMBER: P3AS13R459740DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1269915

CATALOG NUMBER: P3AS13R459740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99181
5°	96918
10°	89422
15°	77753
20°	63869
25°	49696
30°	36689
35°	25832
40°	16116
45°	8745
50°	4708
55°	4052
60°	3640
65°	3113
70°	2693
75°	2711
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8745 cd/sqm

TEST NUMBER: P1269915

CATALOG NUMBER: P3AS13R459740DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.8	12.2
10°-20°	94.7	28.4
20°-30°	94.0	28.2
30°-40°	60.5	18.2
40°-50°	23.3	7.0
50°-60°	9.5	2.8
60°-70°	6.0	1.8
70°-80°	3.2	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	229.4	68.9
0°-40°	290.0	87.1
0°-60°	322.7	96.9
0°-90°	333.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	333.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	452	
5°	440	41
15°	342	95
25°	205	94
35°	96	61
45°	28	23
55°	11	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1269915

CATALOG NUMBER: P3AS13R459740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	452.3
2.5°	450.0
5°	440.3
7.5°	423.7
10°	401.6
12.5°	373.9
15°	342.5
17.5°	308.3
20°	273.7
22.5°	238.6
25°	205.4
27.5°	174.0
30°	144.9
32.5°	119.5
35°	96.5
37.5°	75.7
40°	56.3
42.5°	40.6
45°	28.2
47.5°	18.9
50°	13.8
52.5°	11.5
55°	10.6
57.5°	9.2
60°	8.3
62.5°	6.9
65°	6.0
67.5°	5.1
70°	4.2
72.5°	3.7
75°	3.2
77.5°	2.3
80°	1.8
82.5°	1.4
85°	0.9
87.5°	0.5
90°	0.0

(END OF REPORT)