

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269995

Luminaire Tested: P3AS13R609740DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269995
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609740DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 990.0 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269995
CATALOG NUMBER: P3AS13R609740DE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1269995
 CATALOG NUMBER: P3AS13R609740DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73			73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63			63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	233775
5°	231564
10°	224801
15°	210626
20°	186426
25°	155936
30°	122221
35°	88660
40°	58996
45°	36779
50°	19888
55°	5773
60°	5350
65°	4877
70°	4809
75°	4745
80°	4799
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 36779 cd/sqm



TEST NUMBER: P1269995
 CATALOG NUMBER: P3AS13R609740DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.1	10.0
10°-20°	257.4	26.0
20°-30°	293.4	29.6
30°-40°	208.0	21.0
40°-50°	94.4	9.5
50°-60°	20.0	2.0
60°-70°	9.7	1.0
70°-80°	5.9	0.6
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	649.8	65.6
0°-40°	857.9	86.7
0°-60°	972.3	98.2
0°-90°	990.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	990.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1066	
5°	1052	99
15°	928	257
25°	644	293
35°	331	208
45°	119	94
55°	15	20
65°	9	10
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1269995
CATALOG NUMBER: P3AS13R609740DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1066.1
2.5°	1062.3
5°	1052.0
7.5°	1034.1
10°	1009.6
12.5°	974.8
15°	927.8
17.5°	868.5
20°	798.9
22.5°	723.6
25°	644.5
27.5°	563.6
30°	482.7
32.5°	405.5
35°	331.2
37.5°	265.3
40°	206.1
42.5°	156.2
45°	118.6
47.5°	88.4
50°	58.3
52.5°	27.3
55°	15.1
57.5°	13.2
60°	12.2
62.5°	11.3
65°	9.4
67.5°	8.5
70°	7.5
72.5°	6.6
75°	5.6
77.5°	4.7
80°	3.8
82.5°	2.8
85°	1.9
87.5°	0.9
90°	0.0

(END OF REPORT)