

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270013

Luminaire Tested: P3AS13R659740DE010 E3CD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659740DE010 E3CD1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1164.0 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270013
CATALOG NUMBER: P3AS13R659740DE010 E3CD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1270013
 CATALOG NUMBER: P3AS13R659740DE010 E3CD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.6	9.9
10°-20°	319.4	27.4
20°-30°	418.1	35.9
30°-40°	242.2	20.8
40°-50°	51.8	4.5
50°-60°	8.4	0.7
60°-70°	4.6	0.4
70°-80°	2.7	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	853.1	73.3
0°-40°	1095.3	94.1
0°-60°	1155.6	99.3
0°-90°	1164.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1164.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1297	
5°	1216	116
15°	1144	319
25°	940	418
35°	382	242
45°	61	52
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1270013
CATALOG NUMBER: P3AS13R659740DE010 E3CD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1297.2
2.5°	1260.5
5°	1216.3
7.5°	1198.4
10°	1187.1
12.5°	1171.1
15°	1143.8
17.5°	1101.4
20°	1050.6
22.5°	1002.6
25°	940.4
27.5°	835.9
30°	698.5
32.5°	541.3
35°	382.2
37.5°	241.9
40°	144.0
42.5°	90.4
45°	61.2
47.5°	39.5
50°	21.7
52.5°	10.4
55°	7.5
57.5°	6.6
60°	5.6
62.5°	5.6
65°	4.7
67.5°	3.8
70°	3.8
72.5°	2.8
75°	2.8
77.5°	1.9
80°	1.9
82.5°	0.9
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)