

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270779

Luminaire Tested: P3AS20R709740D010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270779
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709740D010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1177.0 lumens
Efficiency: N/A
Efficacy: 40.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270779

CATALOG NUMBER: P3AS20R709740D010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1270779

CATALOG NUMBER: P3AS20R709740D010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50			
RCR																				0		
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94	92
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86	84
3	100	93	88	83		98	92	87	83		89	85	81		87	83	80		84	81	79	77
4	95	86	80	76		93	85	80	75		83	78	74		81	77	73		79	76	73	71
5	89	80	74	69		88	79	73	69		78	72	68		76	71	68		74	70	67	65
6	85	75	68	64		83	74	68	64		73	67	63		71	66	63		70	65	62	61
7	80	70	64	59		79	69	63	59		68	62	58		67	62	58		66	61	58	56
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54	52
9	72	62	55	51		71	61	55	51		60	55	51		59	54	51		58	54	50	49
10	69	58	52	48		67	58	52	48		57	51	48		56	51	48		55	51	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	276074
5°	271010
10°	255551
15°	231920
20°	202878
25°	171131
30°	140123
35°	108683
40°	77803
45°	49245
50°	24562
55°	15025
60°	12938
65°	11882
70°	10515
75°	9743
80°	8208
85°	8303

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 49245 cd/sqm

TEST NUMBER: P1270779

CATALOG NUMBER: P3AS20R709740D010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.9	9.8
10°-20°	284.3	24.2
20°-30°	323.8	27.5
30°-40°	253.2	21.5
40°-50°	124.4	10.6
50°-60°	38.3	3.3
60°-70°	22.7	1.9
70°-80°	12.1	1.0
80°-90°	3.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	722.9	61.4
0°-40°	976.1	82.9
0°-60°	1138.7	96.7
0°-90°	1177.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1177.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1259	
5°	1231	115
15°	1022	284
25°	707	324
35°	406	253
45°	159	124
55°	39	38
65°	23	23
75°	12	12
85°	3	4
90°	0	

TEST NUMBER: P1270779

CATALOG NUMBER: P3AS20R709740D010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1259.0
2.5°	1252.5
5°	1231.2
7.5°	1196.8
10°	1147.7
12.5°	1090.4
15°	1021.6
17.5°	947.9
20°	869.4
22.5°	787.5
25°	707.3
27.5°	628.7
30°	553.4
32.5°	478.1
35°	406.0
37.5°	337.3
40°	271.8
42.5°	211.2
45°	158.8
47.5°	111.3
50°	72.0
52.5°	47.5
55°	39.3
57.5°	34.4
60°	29.5
62.5°	26.2
65°	22.9
67.5°	19.6
70°	16.4
72.5°	13.1
75°	11.5
77.5°	9.8
80°	6.5
82.5°	4.9
85°	3.3
87.5°	1.6
90°	0.0

(END OF REPORT)