

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270021

Luminaire Tested: P3AS13R659740DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270021
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659740DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 943.9 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270021
CATALOG NUMBER: P3AS13R659740DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1270021
 CATALOG NUMBER: P3AS13R659740DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63				63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58				58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48				48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	222614
5°	219942
10°	211597
15°	198230
20°	178282
25°	151388
30°	118398
35°	84377
40°	55218
45°	34143
50°	17330
55°	6117
60°	5350
65°	5344
70°	4809
75°	4745
80°	4799
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34143 cd/sqm



TEST NUMBER: P1270021
 CATALOG NUMBER: P3AS13R659740DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.8	9.9
10°-20°	243.0	25.7
20°-30°	284.0	30.1
30°-40°	198.5	21.0
40°-50°	87.3	9.3
50°-60°	19.4	2.1
60°-70°	9.9	1.0
70°-80°	5.9	0.6
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	620.8	65.8
0°-40°	819.3	86.8
0°-60°	926.1	98.1
0°-90°	943.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	943.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1015	
5°	999	94
15°	873	243
25°	626	284
35°	315	198
45°	110	87
55°	16	19
65°	10	10
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1270021
CATALOG NUMBER: P3AS13R659740DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1015.2
2.5°	1011.5
5°	999.2
7.5°	978.5
10°	950.3
12.5°	915.5
15°	873.2
17.5°	821.4
20°	764.0
22.5°	699.1
25°	625.7
27.5°	548.5
30°	467.6
32.5°	389.5
35°	315.2
37.5°	250.3
40°	192.9
42.5°	145.8
45°	110.1
47.5°	80.9
50°	50.8
52.5°	26.3
55°	16.0
57.5°	14.1
60°	12.2
62.5°	11.3
65°	10.3
67.5°	8.5
70°	7.5
72.5°	6.6
75°	5.6
77.5°	4.7
80°	3.8
82.5°	2.8
85°	1.9
87.5°	0.9
90°	0.0

(END OF REPORT)