

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270839

Luminaire Tested: P3AS02R159827DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159827DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 173.0 lumens
Efficiency: N/A
Efficacy: 48.1 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270839

CATALOG NUMBER: P3AS02R159827DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1270839

CATALOG NUMBER: P3AS02R159827DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	103	100		108	104	101	99		101	99	97		98	96	95		96	94	93
3	106	101	97	93		104	99	96	93		97	94	91		94	92	90		92	90	88
4	102	96	92	88		100	95	91	88		93	89	87		91	88	86		89	87	85
5	98	92	87	84		97	91	87	83		89	86	83		88	84	82		86	83	81
6	95	88	83	80		94	87	83	80		86	82	79		85	81	79		83	80	78
7	92	85	80	77		91	84	80	76		83	79	76		82	78	76		81	78	75
8	89	81	77	74		88	81	77	73		80	76	73		79	76	73		78	75	73
9	86	79	74	71		85	78	74	71		77	73	71		77	73	70		76	73	70
10	84	76	71	68		83	76	71	68		75	71	68		74	71	68		74	70	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147795
5°	131191
10°	91092
15°	53871
20°	30686
25°	17541
30°	9698
35°	5166
40°	2863
45°	1551
50°	955
55°	765
60°	658
65°	623
70°	513
75°	593
80°	379
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1551 cd/sqm

TEST NUMBER: P1270839

CATALOG NUMBER: P3AS02R159827DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.7	29.3
10°-20°	66.9	38.7
20°-30°	34.4	19.9
30°-40°	12.9	7.5
40°-50°	4.2	2.5
50°-60°	1.8	1.1
60°-70°	1.1	0.7
70°-80°	0.7	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	152.0	87.9
0°-40°	164.9	95.3
0°-60°	171.0	98.8
0°-90°	173.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	173.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	674	
5°	596	51
15°	237	67
25°	72	34
35°	19	13
45°	5	4
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1270839

CATALOG NUMBER: P3AS02R159827DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	674.0
1°	672.6
2°	663.8
3°	647.0
4°	624.8
5°	596.0
6°	563.3
7°	527.5
8°	487.6
9°	448.3
10°	409.1
12.5°	314.8
15°	237.3
17.5°	177.7
20°	131.5
22.5°	98.2
25°	72.5
27.5°	52.8
30°	38.3
32.5°	27.2
35°	19.3
37.5°	13.8
40°	10.0
42.5°	7.2
45°	5.0
47.5°	3.7
50°	2.8
52.5°	2.3
55°	2.0
57.5°	1.7
60°	1.5
62.5°	1.3
65°	1.2
67.5°	1.0
70°	0.8
72.5°	0.8
75°	0.7
77.5°	0.5
80°	0.3
82.5°	0.3
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)