

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270840

Luminaire Tested: P3AS02R159827DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270840
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159827DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 103.0 lumens
Efficiency: N/A
Efficacy: 28.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270840

CATALOG NUMBER: P3AS02R159827DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1270840

CATALOG NUMBER: P3AS02R159827DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		68
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44426
5°	41052
10°	32776
15°	24767
20°	18855
25°	14372
30°	10280
35°	6719
40°	4122
45°	2481
50°	1672
55°	1262
60°	1096
65°	934
70°	833
75°	847
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2481 cd/sqm

TEST NUMBER: P1270840

CATALOG NUMBER: P3AS02R159827DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.5	16.0
10°-20°	30.5	29.6
20°-30°	27.1	26.3
30°-40°	16.0	15.6
40°-50°	6.6	6.4
50°-60°	3.1	3.0
60°-70°	1.9	1.8
70°-80°	1.0	1.0
80°-90°	0.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	74.2	72.0
0°-40°	90.2	87.6
0°-60°	99.9	97.0
0°-90°	103.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	103.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	203	
5°	186	17
15°	109	30
25°	59	27
35°	25	16
45°	8	7
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1270840

CATALOG NUMBER: P3AS02R159827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	202.6
1°	202.1
2°	200.5
3°	197.5
4°	192.5
5°	186.5
6°	180.0
7°	172.3
8°	164.2
9°	156.1
10°	147.2
12.5°	127.0
15°	109.1
17.5°	93.7
20°	80.8
22.5°	69.4
25°	59.4
27.5°	49.7
30°	40.6
32.5°	32.4
35°	25.1
37.5°	19.2
40°	14.4
42.5°	10.7
45°	8.0
47.5°	6.2
50°	4.9
52.5°	4.0
55°	3.3
57.5°	2.8
60°	2.5
62.5°	2.2
65°	1.8
67.5°	1.7
70°	1.3
72.5°	1.2
75°	1.0
77.5°	0.7
80°	0.5
82.5°	0.3
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)