

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270079

Luminaire Tested: P3AS17R159740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270079
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 482.0 lumens
Efficiency: N/A
Efficacy: 22.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270079

CATALOG NUMBER: P3AS17R159740DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1270079

CATALOG NUMBER: P3AS17R159740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	70	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121569
5°	118270
10°	108081
15°	94688
20°	81230
25°	67818
30°	54262
35°	40689
40°	29541
45°	19320
50°	12076
55°	8181
60°	7236
65°	6641
70°	6283
75°	5676
80°	5430
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19320 cd/sqm

TEST NUMBER: P1270079

CATALOG NUMBER: P3AS17R159740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	10.3
10°-20°	116.2	24.1
20°-30°	128.0	26.6
30°-40°	95.9	19.9
40°-50°	49.7	10.3
50°-60°	20.6	4.3
60°-70°	12.8	2.6
70°-80°	7.2	1.5
80°-90°	2.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.8	61.0
0°-40°	389.7	80.8
0°-60°	460.0	95.4
0°-90°	482.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	482.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	554	
5°	537	50
15°	417	116
25°	280	128
35°	152	96
45°	62	50
55°	21	21
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1270079

CATALOG NUMBER: P3AS17R159740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	554.4
1°	555.1
2°	553.2
3°	549.6
4°	544.1
5°	537.3
6°	528.8
7°	519.6
8°	508.6
9°	497.0
10°	485.4
12.5°	451.9
15°	417.1
17.5°	382.2
20°	348.1
22.5°	313.2
25°	280.3
27.5°	247.3
30°	214.3
32.5°	182.0
35°	152.0
37.5°	126.4
40°	103.2
42.5°	81.8
45°	62.3
47.5°	47.0
50°	35.4
52.5°	26.3
55°	21.4
57.5°	18.9
60°	16.5
62.5°	14.7
65°	12.8
67.5°	11.0
70°	9.8
72.5°	7.9
75°	6.7
77.5°	5.5
80°	4.3
82.5°	3.1
85°	1.8
87.5°	0.6
90°	0.0

(END OF REPORT)