

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270866

Luminaire Tested: P3AS02R209827DE010 E3DLP1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1270866  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R209827DE010 E3DLP1WH  
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 98CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 172.0 lumens  
Efficiency: N/A  
Efficacy: 47.8 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270866  
CATALOG NUMBER: P3AS02R209827DE010 E3DLP1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1270866

CATALOG NUMBER: P3AS02R209827DE010 E3DLP1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97		95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92		91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88		87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84		83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81		79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77		76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75		73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72		71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69		68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67		66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	132336
5°	120295
10°	88910
15°	55006
20°	31409
25°	17928
30°	10052
35°	5461
40°	3006
45°	1644
50°	955
55°	688
60°	658
65°	623
70°	513
75°	593
80°	379
85°	503

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1644 cd/sqm



TEST NUMBER: P1270866  
 CATALOG NUMBER: P3AS02R209827DE010 E3DLP1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.3	27.5
10°-20°	67.6	39.3
20°-30°	35.3	20.5
30°-40°	13.6	7.9
40°-50°	4.4	2.6
50°-60°	1.8	1.0
60°-70°	1.1	0.7
70°-80°	0.7	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	150.2	87.3
0°-40°	163.8	95.2
0°-60°	170.0	98.8
0°-90°	172.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	172.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	604	
5°	546	47
15°	242	68
25°	74	35
35°	20	14
45°	5	4
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1270866  
CATALOG NUMBER: P3AS02R209827DE010 E3DLP1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	603.5
1°	602.3
2°	595.2
3°	584.2
4°	567.3
5°	546.5
6°	521.9
7°	494.7
8°	463.1
9°	432.3
10°	399.3
12.5°	317.4
15°	242.3
17.5°	181.3
20°	134.6
22.5°	99.7
25°	74.1
27.5°	54.7
30°	39.7
32.5°	28.7
35°	20.4
37.5°	14.8
40°	10.5
42.5°	7.5
45°	5.3
47.5°	3.8
50°	2.8
52.5°	2.2
55°	1.8
57.5°	1.7
60°	1.5
62.5°	1.3
65°	1.2
67.5°	1.0
70°	0.8
72.5°	0.8
75°	0.7
77.5°	0.5
80°	0.3
82.5°	0.3
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)