

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270880

Luminaire Tested: P3AS02R259827DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270880
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259827DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 98CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 225.0 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270880

CATALOG NUMBER: P3AS02R259827DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1270880

CATALOG NUMBER: P3AS02R259827DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		100
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	106	101	97	94	104	99	96	94	98	95	92		96	93	91		94
5	103	97	93	91	101	96	93	90	95	92	89		93	91	89		92
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		90
7	98	92	88	85	97	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	83	88	85	82		87	84	82		86
9	93	87	83	81	92	86	83	80	86	83	80		85	82	80		84
10	91	85	81	79	90	84	81	79	84	81	78		83	80	78		83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	246428
5°	228263
10°	176617
15°	84359
20°	27816
25°	11735
30°	4532
35°	1954
40°	658
45°	310
50°	102
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 310 cd/sqm

TEST NUMBER: P1270880

CATALOG NUMBER: P3AS02R259827DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.2	40.5
10°-20°	103.7	46.1
20°-30°	24.1	10.7
30°-40°	5.0	2.2
40°-50°	0.8	0.4
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	218.9	97.3
0°-40°	224.0	99.5
0°-60°	225.0	100.0
0°-90°	225.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	225.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1124	
5°	1037	91
15°	372	104
25°	48	24
35°	7	5
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1270880

CATALOG NUMBER: P3AS02R259827DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1123.8
1°	1121.5
2°	1109.8
3°	1093.4
4°	1068.4
5°	1037.0
6°	996.8
7°	954.7
8°	907.5
9°	854.2
10°	793.2
11°	722.5
12°	641.3
13°	552.4
14°	459.4
15°	371.6
16°	293.9
17°	229.0
18°	180.1
19°	144.1
20°	119.2
21°	99.6
22°	83.6
23°	69.8
24°	58.4
25°	48.5
27.5°	28.7
30°	17.9
32.5°	11.5
35°	7.3
37.5°	4.4
40°	2.3
42.5°	1.5
45°	1.0
47.5°	0.6
50°	0.3
52.5°	0.2
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.0
72.5°	0.0

TEST NUMBER: P1270880

CATALOG NUMBER: P3AS02R259827DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)