

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270884

Luminaire Tested: P3AS02R259827DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270884
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259827DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 98CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 174.0 lumens
Efficiency: N/A
Efficacy: 48.3 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270884

CATALOG NUMBER: P3AS02R259827DE010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1270884

CATALOG NUMBER: P3AS02R259827DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	86	81	78		84	80	77		83	79	77		82	78	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	75	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	68		73	70	67
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	111614
5°	104138
10°	83410
15°	56618
20°	34256
25°	20033
30°	11419
35°	6264
40°	3321
45°	1768
50°	1023
55°	765
60°	658
65°	675
70°	641
75°	593
80°	379
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1768 cd/sqm

TEST NUMBER: P1270884

CATALOG NUMBER: P3AS02R259827DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.0	24.1
10°-20°	68.6	39.4
20°-30°	39.2	22.5
30°-40°	15.5	8.9
40°-50°	4.8	2.7
50°-60°	1.9	1.1
60°-70°	1.3	0.7
70°-80°	0.7	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	149.7	86.1
0°-40°	165.2	94.9
0°-60°	171.8	98.7
0°-90°	174.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	174.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	509	
5°	473	42
15°	249	69
25°	83	39
35°	23	15
45°	6	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1270884

CATALOG NUMBER: P3AS02R259827DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	509.0
1°	508.0
2°	503.8
3°	496.5
4°	486.4
5°	473.1
6°	457.5
7°	439.8
8°	419.4
9°	398.4
10°	374.6
11°	351.2
12°	325.4
13°	300.0
14°	273.9
15°	249.4
17.5°	193.4
20°	146.8
22.5°	110.2
25°	82.8
27.5°	61.4
30°	45.1
32.5°	32.6
35°	23.4
37.5°	16.6
40°	11.6
42.5°	8.0
45°	5.7
47.5°	4.0
50°	3.0
52.5°	2.3
55°	2.0
57.5°	1.8
60°	1.5
62.5°	1.3
65°	1.3
67.5°	1.2
70°	1.0
72.5°	0.8
75°	0.7
77.5°	0.5
80°	0.3
82.5°	0.3
85°	0.2
87.5°	0.2



TEST NUMBER: P1270884

CATALOG NUMBER: P3AS02R259827DE010 E3DL1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)