

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270182

Luminaire Tested: P3AS17R309740DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270182
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309740DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 970.0 lumens
Efficiency: N/A
Efficacy: 45.8 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270182
CATALOG NUMBER: P3AS17R309740DE010 E3PHLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1270182
 CATALOG NUMBER: P3AS17R309740DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80			
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	71			
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65			
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59			
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50			
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	48	46			
9	68	57	50	45	66	56	49	45	55	49	45	54	49	45	53	48	44	43			
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	239016
5°	228461
10°	197057
15°	163338
20°	133898
25°	107934
30°	87001
35°	71260
40°	59225
45°	50207
50°	42950
55°	37122
60°	33111
65°	28953
70°	25389
75°	21350
80°	15911
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 50207 cd/sqm



TEST NUMBER: P1270182
 CATALOG NUMBER: P3AS17R309740DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	9.7
10°-20°	200.6	20.7
20°-30°	205.6	21.2
30°-40°	168.1	17.3
40°-50°	125.7	13.0
50°-60°	88.3	9.1
60°-70°	55.6	5.7
70°-80°	26.8	2.8
80°-90°	5.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	500.4	51.6
0°-40°	668.5	68.9
0°-60°	882.5	91.0
0°-90°	970.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	970.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1090	
5°	1038	94
15°	720	201
25°	446	206
35°	266	168
45°	162	126
55°	97	88
65°	56	56
75°	25	27
85°	4	5
90°	0	



TEST NUMBER: P1270182
CATALOG NUMBER: P3AS17R309740DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1090.0
2.5°	1079.2
5°	1037.9
7.5°	969.5
10°	885.0
12.5°	802.2
15°	719.5
17.5°	643.9
20°	573.8
22.5°	507.2
25°	446.1
27.5°	392.1
30°	343.6
32.5°	304.0
35°	266.2
37.5°	235.6
40°	206.9
42.5°	183.5
45°	161.9
47.5°	142.1
50°	125.9
52.5°	111.5
55°	97.1
57.5°	86.3
60°	75.5
62.5°	64.8
65°	55.8
67.5°	46.8
70°	39.6
72.5°	32.4
75°	25.2
77.5°	18.0
80°	12.6
82.5°	7.2
85°	3.6
87.5°	1.8
90°	0.0

(END OF REPORT)