

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270898

Luminaire Tested: P3AS02R259827DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270898
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259827DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 107.0 lumens
Efficiency: N/A
Efficacy: 29.7 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270898

CATALOG NUMBER: P3AS02R259827DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1270898

CATALOG NUMBER: P3AS02R259827DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38857
5°	37266
10°	32642
15°	26243
20°	20162
25°	15267
30°	11014
35°	7335
40°	4437
45°	2574
50°	1637
55°	1338
60°	1184
65°	1038
70°	833
75°	847
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2574 cd/sqm

TEST NUMBER: P1270898

CATALOG NUMBER: P3AS02R259827DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.4	14.4
10°-20°	32.0	29.9
20°-30°	28.9	27.0
30°-40°	17.4	16.2
40°-50°	6.9	6.4
50°-60°	3.2	3.0
60°-70°	2.0	1.8
70°-80°	1.0	1.0
80°-90°	0.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	76.3	71.3
0°-40°	93.7	87.6
0°-60°	103.7	96.9
0°-90°	107.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	107.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	177	
5°	169	15
15°	116	32
25°	63	29
35°	27	17
45°	8	7
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1270898

CATALOG NUMBER: P3AS02R259827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	177.2
1°	177.2
2°	176.3
3°	174.5
4°	172.2
5°	169.3
6°	165.6
7°	161.5
8°	156.6
9°	151.8
10°	146.6
11°	140.6
12°	134.5
13°	128.3
14°	122.1
15°	115.6
17.5°	100.3
20°	86.4
22.5°	73.9
25°	63.1
27.5°	52.9
30°	43.5
32.5°	35.0
35°	27.4
37.5°	20.9
40°	15.5
42.5°	11.3
45°	8.3
47.5°	6.3
50°	4.8
52.5°	4.0
55°	3.5
57.5°	3.0
60°	2.7
62.5°	2.2
65°	2.0
67.5°	1.7
70°	1.3
72.5°	1.2
75°	1.0
77.5°	0.8
80°	0.5
82.5°	0.3
85°	0.3
87.5°	0.2



TEST NUMBER: P1270898

CATALOG NUMBER: P3AS02R259827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)