

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270935

Luminaire Tested: P3AS02R359827DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270935
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359827DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 98CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 211.0 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270935

CATALOG NUMBER: P3AS02R359827DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1270935

CATALOG NUMBER: P3AS02R359827DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83		
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	77		
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75		
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73		
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	137577
5°	134778
10°	125382
15°	91919
20°	47067
25°	16961
30°	6609
35°	2302
40°	945
45°	248
50°	239
55°	268
60°	219
65°	156
70°	192
75°	254
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 336 cd/sqm

TEST NUMBER: P1270935

CATALOG NUMBER: P3AS02R359827DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.1	27.1
10°-20°	107.1	50.8
20°-30°	37.9	18.0
30°-40°	6.6	3.1
40°-50°	1.0	0.5
50°-60°	0.6	0.3
60°-70°	0.4	0.2
70°-80°	0.3	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	202.1	95.8
0°-40°	208.7	98.9
0°-60°	210.3	99.7
0°-90°	211.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	211.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	627	
5°	612	57
15°	405	107
25°	70	38
35°	9	7
45°	1	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1270935

CATALOG NUMBER: P3AS02R359827DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	627.4
1°	627.3
2°	625.3
3°	621.5
4°	618.0
5°	612.3
6°	606.5
7°	600.0
8°	592.0
9°	579.6
10°	563.1
11°	540.4
12°	513.0
13°	480.4
14°	444.5
15°	404.9
17.5°	301.6
20°	201.7
22.5°	121.6
25°	70.1
27.5°	41.9
30°	26.1
32.5°	15.1
35°	8.6
37.5°	5.5
40°	3.3
42.5°	1.7
45°	0.8
47.5°	0.7
50°	0.7
52.5°	0.7
55°	0.7
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0



TEST NUMBER: P1270935
CATALOG NUMBER: P3AS02R359827DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)