

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270232

Luminaire Tested: P3AS17R409740DE010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1270232  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R409740DE010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1114.0 lumens  
Efficiency: N/A  
Efficacy: 52.5 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1270232

CATALOG NUMBER: P3AS17R409740DE010 E3DLD1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1270232

CATALOG NUMBER: P3AS17R409740DE010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 94  | 93  | 91  |    |    |
| 2   | 106 | 100 | 96  | 92  | 104 | 98  | 94  | 91  | 95  | 92  | 89  | 92  | 89  | 87  | 89  | 87  | 85  | 83  |    |    |
| 3   | 100 | 92  | 87  | 82  | 98  | 91  | 86  | 81  | 88  | 84  | 80  | 86  | 82  | 79  | 83  | 80  | 78  | 76  |    |    |
| 4   | 94  | 85  | 79  | 74  | 92  | 84  | 78  | 74  | 82  | 77  | 73  | 80  | 75  | 72  | 78  | 74  | 71  | 69  |    |    |
| 5   | 89  | 79  | 73  | 68  | 87  | 78  | 72  | 67  | 76  | 71  | 67  | 75  | 70  | 66  | 73  | 69  | 66  | 64  |    |    |
| 6   | 84  | 74  | 67  | 62  | 82  | 73  | 67  | 62  | 71  | 66  | 61  | 70  | 65  | 61  | 68  | 64  | 61  | 59  |    |    |
| 7   | 79  | 69  | 62  | 57  | 78  | 68  | 62  | 57  | 67  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 56  | 55  |    |    |
| 8   | 75  | 64  | 58  | 53  | 74  | 64  | 57  | 53  | 63  | 57  | 53  | 62  | 56  | 53  | 61  | 56  | 52  | 51  |    |    |
| 9   | 71  | 60  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 53  | 49  | 58  | 53  | 49  | 57  | 52  | 49  | 48  |    |    |
| 10  | 67  | 57  | 51  | 46  | 66  | 56  | 50  | 46  | 56  | 50  | 46  | 55  | 50  | 46  | 54  | 49  | 46  | 45  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 250068 |
| 5°  | 245542 |
| 10° | 231459 |
| 15° | 210217 |
| 20° | 184676 |
| 25° | 157703 |
| 30° | 130653 |
| 35° | 100759 |
| 40° | 71706  |
| 45° | 48315  |
| 50° | 26370  |
| 55° | 18580  |
| 60° | 17499  |
| 65° | 16189  |
| 70° | 14361  |
| 75° | 13725  |
| 80° | 10986  |
| 85° | 9309   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 48315 cd/sqm

TEST NUMBER: P1270232

CATALOG NUMBER: P3AS17R409740DE010 E3DLD1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 104.0  | 9.3       |
| 10°-20°   | 258.0  | 23.2      |
| 20°-30°   | 298.2  | 26.8      |
| 30°-40°   | 235.0  | 21.1      |
| 40°-50°   | 120.6  | 10.8      |
| 50°-60°   | 46.1   | 4.1       |
| 60°-70°   | 30.5   | 2.7       |
| 70°-80°   | 16.6   | 1.5       |
| 80°-90°   | 4.9    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 660.2  | 59.3      |
| 0°-40°    | 895.2  | 80.4      |
| 0°-60°    | 1062.0 | 95.3      |
| 0°-90°    | 1114.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1114.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1140 |      |
| 5°  | 1116 | 104  |
| 15° | 926  | 258  |
| 25° | 652  | 298  |
| 35° | 376  | 235  |
| 45° | 156  | 121  |
| 55° | 49   | 46   |
| 65° | 31   | 31   |
| 75° | 16   | 17   |
| 85° | 4    | 5    |
| 90° | 0    |      |

TEST NUMBER: P1270232

CATALOG NUMBER: P3AS17R409740DE010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1140.4 |
| 2.5°  | 1134.2 |
| 5°    | 1115.5 |
| 7.5°  | 1083.1 |
| 10°   | 1039.5 |
| 12.5° | 988.4  |
| 15°   | 926.0  |
| 17.5° | 861.2  |
| 20°   | 791.4  |
| 22.5° | 720.4  |
| 25°   | 651.8  |
| 27.5° | 583.3  |
| 30°   | 516.0  |
| 32.5° | 447.4  |
| 35°   | 376.4  |
| 37.5° | 310.3  |
| 40°   | 250.5  |
| 42.5° | 199.4  |
| 45°   | 155.8  |
| 47.5° | 113.4  |
| 50°   | 77.3   |
| 52.5° | 56.1   |
| 55°   | 48.6   |
| 57.5° | 43.6   |
| 60°   | 39.9   |
| 62.5° | 34.9   |
| 65°   | 31.2   |
| 67.5° | 26.2   |
| 70°   | 22.4   |
| 72.5° | 18.7   |
| 75°   | 16.2   |
| 77.5° | 12.5   |
| 80°   | 8.7    |
| 82.5° | 7.5    |
| 85°   | 3.7    |
| 87.5° | 2.5    |
| 90°   | 0.0    |

(END OF REPORT)