

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1270240

Luminaire Tested: P3AS17R409740DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1270240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409740DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 916.0 lumens
Efficiency: N/A
Efficacy: 43.2 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1270240

CATALOG NUMBER: P3AS17R409740DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1270240

CATALOG NUMBER: P3AS17R409740DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	285218
5°	279440
10°	260182
15°	226766
20°	182763
25°	136992
30°	96319
35°	63095
40°	38186
45°	22824
50°	13611
55°	10972
60°	9824
65°	8406
70°	8014
75°	6354
80°	6314
85°	6290

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22824 cd/sqm

TEST NUMBER: P1270240

CATALOG NUMBER: P3AS17R409740DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.9	12.9
10°-20°	275.1	30.0
20°-30°	259.3	28.3
30°-40°	149.9	16.4
40°-50°	59.7	6.5
50°-60°	26.4	2.9
60°-70°	16.3	1.8
70°-80°	8.6	0.9
80°-90°	2.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	652.3	71.2
0°-40°	802.2	87.6
0°-60°	888.4	97.0
0°-90°	916.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	916.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1301	
5°	1270	118
15°	999	275
25°	566	259
35°	236	150
45°	74	60
55°	29	26
65°	16	16
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1270240

CATALOG NUMBER: P3AS17R409740DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1300.7
2.5°	1293.2
5°	1269.5
7.5°	1225.9
10°	1168.5
12.5°	1091.2
15°	998.9
17.5°	895.4
20°	783.2
22.5°	670.9
25°	566.2
27.5°	468.9
30°	380.4
32.5°	303.0
35°	235.7
37.5°	178.3
40°	133.4
42.5°	99.8
45°	73.6
47.5°	53.6
50°	39.9
52.5°	32.4
55°	28.7
57.5°	26.2
60°	22.4
62.5°	18.7
65°	16.2
67.5°	13.7
70°	12.5
72.5°	10.0
75°	7.5
77.5°	6.2
80°	5.0
82.5°	3.7
85°	2.5
87.5°	1.2
90°	0.0

(END OF REPORT)